

Knurl cutter holder model LA/FL C601

For knurl cutting on lathes and automatic lathes



Application:

For producing knurl cutting profiles in accordance with DIN 82 RAA, RBR 15°, RBL 15°, RBR 30° and RBL 30° in steel, stainless steel, non-ferrous metals and cast iron material groups.

Execution:

- high-strength steel tool holder for one knurl cutter, with cemented carbide bushings

Advantage:

- Compact and robust holder design for high process stability for small components
- User-friendly setting without disassembly
- cemented carbide bushings minimise maintenance costs



Art. no.	19100 512
Brand	QUICK
Manufacturer Part Number	32000014
Shaft length	88 mm
For min. workpiece diameter	1.5 mm
For max. workpiece diameter	12 mm
Suitable for knurling wheel diameter	8.9 mm
Min./max. possible division	0.3-1 mm
Shank width	12 mm
Shaft height	12 mm
Tool design	Right
Gross Weight	0.193 kg
Product Group	192