

## Felt polishing and grinding points

Shank diameter 6 mm



### Application:

For pre-polishing and gloss polishing of injection moulding tools, fittings, cemented carbide cutting knives and for gloss polishing of stainless steel components (INOX).

### Advantage:

- Exact preservation of geometric shapes due to its hardness
- Freely profilable and can therefore also be used for tools with complicated geometries
- Exact preservation of geometric shapes due to its hardness



|   |                  |
|---|------------------|
| <b>Art. no.</b>                             | <b>69202 020</b> |
| <b>Brand</b>                                | PFERD            |
| <b>Manufacturer Part Number</b>             | 4007220 153888   |
| <b>Form</b>                                 | Cylindrical      |
| <b>Head diameter x head length</b>          | 25 x 30 mm       |
| <b>Min./max. recommended rotation speed</b> | 4000-8000 rpm    |
| <b>Max. rotation speed</b>                  | 24400 rpm        |
| <b>Number of pieces per packet</b>          | 10 PCS           |
| <b>Gross Weight</b>                         | 0.020 kg         |
| <b>Product Group</b>                        | 6AB              |

### EAN

4007220 153888

