

Pneumatic bore deburring tool BE 805

Up to 24 mm bore diameter



Application:

For deburring bores.

Execution:

- Air discharge to the rear
- With continuously variable speed regulation

Delivery:

Includes collet chuck ZG 7/8 mm, collet chuck key size 11 + 14 and hose unit; in box



Art. no.	78300 020
Brand	BIAX DRUCKLUFT
Manufacturer Part Number	1508 10901
Model	BE 805
Valve design	Thrust start
Motor design	Vane motor
Max. idle speed	500 rpm
Air consumption	280 l/min
Max. clamping diameter	8 mm
Min./max. idle speed	0-500 rpm
Suitable for bore diameter	24 mm
Inner hose diameter	7 mm
Length	231 mm
Diameter of housing	32 mm
Weight	0.52 kg
Spot-facer diameter	25 mm
Max. bore diameter	24 mm
Connection thread	G 1/8 inch
Power output	80 W
With speed control	Yes
Sound-pressure level	71 dB
Gross Weight	1.124 kg
Product Group	748