

Torque wrench with fixed ratchet, adjustable

Standard MANOSKOP® 721 Nf with calibration certificate



Execution:

- Releasing, double stop signal
- Convenient adjustment
- Double scale Nm/ft.lb
- Square reversible for left-hand tightening
- All sensitive parts are protected by the robust steel tube in aluminium U-profile
- Re-adjust without disassembly
- Certificate in line with DIN EN ISO 6789-2:2017
- Display deviation of $\pm 4\%$



Delivery:

In textile bag

Art. no.	52280 080
Brand	STAHLWILLE
Manufacturer Part Number	5020008 1
Tip size	3/4 inch
Max. torque	800 Nm
Min. torque	160 Nm
Scale value torque	5 Nm
Length	1051 mm
Min./max. torque	160-800 Nm
Error limit (%)	4 %
Calibration certificate	Yes
Gross Weight	7.100 kg
Product Group	531

EAN

4018754031979