


Data sheet for General Purpose Toroidal Transformers – 50VA Economy Series



Primary

Dual Primary winding for connection in series or parallel only
 Input voltage : 115V or 230V +/-10% 50/60 Hz
 Dc resistance : 2x 29Ohms +/-20% @ 20 °C
 Magnetising current : 4,3mA @ primary 230V 50Hz
 8,6mA @ primary 115V 50Hz

Losses

Iron loss : 0,512 Watts
 Copper loss : 7,6Watts
 Efficiency : 85% Typical
 Calculated Temperature rise : 52 °C
 (In open environment)
 Maximum rated ambient : 40 °C

Termination

All leads UL1569/UL1015 / 105°C
 Primary leads Double insulated with Insulation Class B tubes, minimum length 20mm
 Lead length Tolerance +/-10mm
 all lead ends 6mm tinned
 All Leads exit at the outer top edge,

Temperature ratings

Winding wire : Class H (180 °C)
 Insulation System : Class B (130 °C)
 Leads insulation : Class A (105 °C)

Degrees of protection : IP00

Ordering code	Art. No.	Load voltage	No load voltage	Rated current	Secondary wire gauge	Sec. DC resistance Ohms @ 20 °C +/-20%
TI-044207-ME-ES	ES0050/6	2 x 6V	2 x 6,9V	2 x 4,17A	AWG16	2 x 0,10
TI-044208-ME-ES	ES0050/9	2 x 9V	2 x 10,3V	2 x 2,78A	AWG18	2 x 0,21
TI-044209-ME-ES	ES0050/12	2 x 12V	2 x 13,7V	2 x 2,08A	AWG20	2 x 0,38
TI-044210-ME-ES	ES0050/15	2 x 15V	2 x 17,1V	2 x 1,67A	AWG20	2 x 0,55
TI-044211-ME-ES	ES0050/18	2 x 18V	2 x 20,4V	2 x 1,39A	AWG20	2 x 0,73
TI-044212-ME-ES	ES0050/25	2 x 25V	2 x 28,6V	2 x 1A	AWG22	2 x 1,61

Approx. Dimensions

Diameter : 78mm
 Inner Diameter : 22mm
 Height : 33mm
 Weight : 0,75kg

Mounting material

1 x Metal washer 50mm
 2 x Rubber pad 50mm
 1 x M5 Screw, nut and washer

Standards

Designed and manufactured in accordance with : EN61558-1 / EN61558-1/A1 / EN61558-2-4 or EN61558-2-6
 UL recognised under family approval E115159 and E20244 to UL1411,UL60601-1,UL1950.

Marking

Model number TI-xxxxxxx ta40/A IP00
 Prim. 2 x 115V 50Hz Fuse XXAT
 Thermal fuse 125 °C
 Sec. 2 x rated voltage and rated current Amp Fuse XXAT
 Art. No. ES0050/XX



Z125