



SIMATIC S7-300, DIGITAL INPUT SM 321, OPTICALLY ISOLATED
32DI, 24 V DC, 1 X 40 PIN

Supply voltage	
Load voltage L+	
• Rated value (DC)	24 V
• permissible range, lower limit (DC)	20.4 V
• permissible range, upper limit (DC)	28.8 V
Input current	
from backplane bus 5 V DC, max.	15 mA
Power losses	
Power loss, typ.	6.5 W
Digital inputs	
Number of digital inputs	32
Input characteristic curve in accordance with IEC 61131, type 1	Yes
horizontal installation	
— up to 40 °C, max.	32
— up to 60 °C, max.	16
vertical installation	
— up to 40 °C, max.	32
Input voltage	
• Type of input voltage	DC
• Rated value (DC)	24 V
• for signal "0"	-30 to +5V
• for signal "1"	13 to 30V
Input current	

• for signal "1", typ.	7 mA
Input delay (for rated value of input voltage)	
for standard inputs	
— Parameterizable	No
— at "0" to "1", min.	1.2 ms
— at "0" to "1", max.	4.8 ms
Cable length	
• shielded, max.	1 000 m
• Unshielded, max.	600 m
Encoder	
Connectable encoders	
• 2-wire sensor	Yes
— Permissible quiescent current (2-wire sensor), max.	1.5 mA
Isochronous mode	
Isochronous operation (application synchronized up to terminal)	No
Interrupts/diagnostics/status information	
Alarms	
• Alarms	No
• Diagnostic alarm	No
• Hardware interrupt	No
Diagnostic messages	
• Diagnostic functions	No
Diagnostics indication LED	
• Status indicator digital input (green)	Yes
Galvanic isolation	
Galvanic isolation digital inputs	
• between the channels	No
• between the channels, in groups of	16
• between the channels and the backplane bus	Yes; Optocoupler
Permissible potential difference	
between different circuits	75V DC/60V AC
Isolation	
Isolation checked with	500 V DC
Connection method	
required front connector	40-pin
Dimensions	
Width	40 mm

Height	125 mm
Depth	120 mm
Weights	
Weight, approx.	260 g
last modified:	12.03.2015