


Clamp Nuts DIN 99 St

Material Version N: Steel, black oxide finish.

Material Stainless: Stainless steel 1.4305 (AISI 303), matt finish blasted.



Handle slanted, with metric thread.



Ordering Details: e.g.: Product No. 665 106 00, Clamp Nut DIN 99, 8 mm

Product No. Version N	Product No. Stainless	d ₁ mm	d ₂ mm	d ₃ mm	l ₁ mm	h mm	b mm	Weight g
665 106 00	665 991 06	8	M6	12	48	24	9,5	17
665 108 00	665 991 08	10	M8	16	60	30,5	12	38
665 110 00	665 991 10	13	M10	20	76	38	14,5	76
665 112 00	665 991 12	16	M12	25	95	47	18,5	144
665 116 00	665 991 16	20	M16	32	119	59,5	24	283
665 120 00	-	25	M20	40	152	76	30	561
665 124 00	-	32	M24	50	190	97	40	1116


Adjustable Clamping Levers 119 St

Material: Steel, black oxide finish.

Version N = handle slanted, with metric thread.

Use: In applications where either the clamping range is limited or where a specific lever position is required. The serrated bore in the spherical hub is fitted with a threaded-bolt insert, which engages in the hub with its own serrations.

By depressing the clamping lever, the serrations are disengaged, freeing it for re-positioning in the most convenient position. When releasing the lever, the serrations re-engage automatically. Should a rotation of 360° not be possible, the insert can be slightly screwed in (after the lever has been disengaged) by means of the slotted knurled screw.



Ordering Details: e.g.: Product No. 665 508 00, Adjustable Clamping Lever 119 St, 10 mm

Product No. Version N	d ₁ mm	d ₂ mm	d ₄ mm	d ₅ mm	h ₁ mm	h ₂ mm	h ₃ mm	l ₂ mm	t mm	Weight g
665 508 00	10	M8	13,5	20	25	8	39,5	60	12	59
665 510 00	13	M10	16	25	29	8	49,5	76	15	118
665 512 00	16	M12	19	28	33,5	10,5	60,5	95	18	188


Clamp Nuts 202 Tg

Material Version N: Cast steel.

Material Stainless: Stainless steel 1.4308 (CF-8), matt finish blasted.



Deburred, contact surface machined. Simple and cost efficient clamping elements.



Ordering Details: e.g.: Product No. 665 308 00, Clamp Nut 202 Tg, version N, 16 mm

Product No. Version N	Product No. Stainless	d ₁ mm	d ₂ mm	a mm	b mm	h ₁ mm	h ₂ ca. mm	l ca. mm	Weight g
665 308 00	665 993 08	16	M8	7	12	12	34	56	30
665 310 00	665 993 10	20	M10	9	14	14	42,5	70	60
665 312 00	665 993 12	25	M12	11	18	18	53	87	125
665 316 00	665 993 16	32	M16	15	22	22	66,5	109	248
665 320 00	665 993 20	40	M20	18	28	28	84,5	140	419