

www.vishay.com

Vishay Spectrol

⁷/₈" (22.2 mm) Multi Turn Wirewound Potentiometer - 533: 3 Turns / 534: 10 Turns / 535: 5 Turns



QUICK REFERENCE DATA							
Sensor type	ROTATIONAL, multi turn wirewound						
Output type	Output by turrets						
Market appliance	Industrial						
Dimensions	⁷ / ₈ " (22.2 mm)						


FEATURES


- · Bushing and servo mount designs available
- Special resistance tolerances to 1 %
- · Rear shaft extensions and support bearing
- Metric shaft available
- · Dual gang configuration and concentric shafts
- High torque, center tap, slipping clutch on request
- · Special markings and front shaft extensions
- Material categorization: for definitions of compliance please see <u>www.vishay.com/doc?99912</u>

ELECTRICAL SPECIFICATIONS									
PARAMETER	MODEL 533	MODEL 534	MODEL 535						
Resistance range - standard values	50 Ω to 20 kΩ	100 Ω to 100 kΩ	50Ω to $50 k\Omega$						
Capability range	5 Ω to 60 kΩ	10 Ω to 200 kΩ	5 Ω to 100 kΩ						
Standard tolerance	± 5 %	± 5 %	± 5 %						
Linearity (independent)	± 0.25 %	± 0.25 %	± 0.25 %						
Noise	100 Ω ENR	100 Ω ENR	100 Ω ENR						
Rotation (electrical and mechanical)	1080° +10° -0°	3600° +10° -0°	1800° +10° -0°						
Power rating (at 70 °C)	1.0 W	2.0 W	1.5 W						
Insulation resistance	1000 M Ω minimum 500 V $_{DC}$								
Dielectric strength	1000 V _{RMS} minimum 60 Hz								
Absolute minimum resistance	Not to exceed linearity x total resistance or 1 Ω , whichever is greater								
Temperature coefficient	20 ppm/°C (standard values, wire only)								
End voltage	0.25 % of total applied voltage, maximum								
Phasing	CCW end points - section 2 phased to section 1 within ± 2°								
Taps	Center tap only								

MARKING	
Unit identification	Manufacturer's name and model number, resistance value and tolerance, linearity specification date code and terminal identification. Example of a marking for a standard part: 534-11103


RESIST	RESISTANCE VALUES									
533 (Ω) 50, 100, 200, 500, 1K, 2K, 5K, 10K, 20K										
534 (Ω)	100, 200, 500, 1K, 2K, 5K, 10K, 20K, 50K, 100K									
535 (Ω)	50, 100, 200, 500, 1K, 2K, 5K, 10K, 20K, 50K									





Revision: 30-Jun-15 1 Document Number: 57065






Mounting hardware, washer and panel nut, nickel plated

MECHANICAL SPECIFICATIONS							
PARAMETER							
Bearing type	Bushing: Sleeve bearing	Servo: Ball bearing					
Torque (maximums): starting Section 1 Section 2	534 0.5 oz in (36 g - cm) 0.9 oz in (65 g - cm)	533/535 0.7 oz in (50 g - cm) 1.1 oz in (79 g - cm)					
Torque (maximums): running Section 1 Section 2	534 0.4 oz in (28.80 g - cm) 0.7 oz in (50.40 g - cm)	533/535 0.6 oz in (43.20 g - cm) 0.9 oz in (64.8 g - cm)					
Weight (maximums) Section1 Section 2		0.75 oz. (21.26 g) 1.25 oz. (35.44 g)					
Stop strength	75 oz in (stat	75 oz in (static) (5.4 kg - cm)					
Ganging	2 sections	2 sections maximum					

POWER RATING CHART



ENVIRONMENTAL SPECIFICATIONS									
Vibration	15 g thru 2000 Hz								
Shock	50 g								
Rotational life (shaft revolution) 533 534 534 (servo) 535	300 000 1 000 000 > 1 000 000 500 000								
Load life	900 h								
Temperature range	-55 °C to +125 °C								

Note

 Nothing stated herein shall be construed as a guarantee of quality or durability.



www.vishay.com

Vishay Spectrol

RESIS	RESISTANCE ELEMENT DATA													
RESISTANCE VALUE (Ω)		RESOLUTION (%)		OHMS PER TURN		MAXIMUM CURRENT AT 70 °C AMBIENT (mA)			MAXIMUM VOLTAGE ACROSS COIL (V)					
533	534	535	533	534	535	533	534	535	533	534	535	533	534	535
50	-	50	0.149	-	0.120	0.0746	-	0.0603	141.0	-	173.0	7.07	-	8.66
100	100	100	0.111	0.060	0.075	0.1114	0.0603	0.0746	100.0	141.0	122.0	10.0	14.1	12.2
200	200	200	0.097	0.037	0.061	0.1954	0.0746	0.1220	70.7	100.0	86.6	14.1	20.0	17.3
500	500	500	0.069	0.031	0.049	0.3424	0.1520	0.2459	44.7	63.2	54.7	22.4	31.6	27.4
1K	1K	1K	0.063	0.025	0.041	0.6331	0.2459	0.4113	31.6	44.7	38.7	31.6	44.7	38.7
2K	2K	2K	0.041	0.021	0.031	0.8206	0.4113	0.6331	22.4	31.6	27.4	44.7	63.2	54.8
5K	5K	5K	0.044	0.016	0.034	2.2330	0.8206	1.7230	14.1	20.0	17.3	70.7	100.0	86.6
10K	10K	10K	0.034	0.017	0.030	3.4510	1.7230	3.0160	10.0	14.1	12.2	100.0	141.0	122.0
20K	20K	20K	0.031	0.015	0.020	6.1790	3.0160	3.9910	7.07	10.0	8.66	141.0	200.0	173.0
-	50K	50K	-	0.009	0.015	-	4.6690	7.4560	-	6.32	5.47	-	316.0	274.0
-	100K	-	-	0.007	-	-	7.4560	-	-	4.47	-	-	447.0	-
-	-	-	-	-	-	-	-	-	-	-	-	-	-	-
-	-	-	-	-	-	-	-	-	-	-	-	-	-	-



Legal Disclaimer Notice

Vishay

Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and/or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.

Material Category Policy

Vishay Intertechnology, Inc. hereby certifies that all its products that are identified as RoHS-Compliant fulfill the definitions and restrictions defined under Directive 2011/65/EU of The European Parliament and of the Council of June 8, 2011 on the restriction of the use of certain hazardous substances in electrical and electronic equipment (EEE) - recast, unless otherwise specified as non-compliant.

Please note that some Vishay documentation may still make reference to RoHS Directive 2002/95/EC. We confirm that all the products identified as being compliant to Directive 2002/95/EC conform to Directive 2011/65/EU.

Vishay Intertechnology, Inc. hereby certifies that all its products that are identified as Halogen-Free follow Halogen-Free requirements as per JEDEC JS709A standards. Please note that some Vishay documentation may still make reference to the IEC 61249-2-21 definition. We confirm that all the products identified as being compliant to IEC 61249-2-21 conform to JEDEC JS709A standards.

Revision: 02-Oct-12 Document Number: 91000