


1	REVISIONS
2	DESCRIPTION \ PER REQUEST \ DATE
3	
4	
5	
6	
7	
8	

ISS	ZONE	DESCRIPTION \ PER REQUEST \ DATE



- NOTES: FINISH (PLATING THICKNESS IN MICRO-INCHES)
1. BRASS PER QQ-B-626
 2. GOLD PL. 3 MIN. THICK OVER NICKEL PL. 100 MIN. THICK OVER COPPER STRIKE
 3. BERYLLIUM COPPER PER QQ-C-530
 4. GOLD PL. 50 MIN. THICK OVER NICKEL PL. 100 MIN. THICK OVER COPPER STRIKE
 5. TEFLON MIL-P-19468

6	CONTACT PIN	NOTE 3	NOTE 4	1	SMAF-RSMAF-6
5	GASKET	SILICONE	RED	1	GS-6/43X06
4	RETAINER RING	NOTE 3	NATURAL	1	SMA5000-4-B
3	INSULATOR	NOTE 5	NATURAL	2	SMA5071A1-3T-50
2	BODY	NOTE 1	NOTE 2	1	SMA5071A1-2-B
1	SHELL	NOTE 1	NOTE 2	1	SMA5000-1-C
NO.	DESCRIPTION	MATERIAL	FINISH	Q'TY	DRAWING NO.

DIMENSIONS ARE IN MILLIMETERS	
UNLESS OTHERWISE SPECIFIED	TOLERANCES
0.5-6 = ±0.2	6-30 = ±0.4
30-120 = ±0.6	120-315 = ±1
315-1000 = ±1.6	1000-2000 = ±2.4
SCALE	5/1
ISSUE	A

PART NO.	
APPROVED	DATE
CHECKED	DATE
DRAWN	DATE

TITLE	
SMA FEMALE TO SMA REVERSE POLARITY FEMALE ADAPTOR	
DRAWING NO.	KJ-SMAF-RSMAF-3GT50G-50
FILE NO.	F:\DWG\SMAF\RSMAF\50\3GT50G

Amphenol - Kai Jack

TAINAN TAIWAN

A

B

C

D

E

F

A

B

C

D

E

F