

## High-performance angular milling cutter 90° with thread

For indexable milling inserts AD.X 0602..

**ATORN**<sup>®</sup>

### Application

High-performance angular milling cutter 90° with thread

### Advantage

- Highly positive indexable insert
- Low power consumption
- precise 90° angular milling



|                                |                  |
|--------------------------------|------------------|
| <b>Art. No.</b>                | <b>16029 026</b> |
| <b>Cutting edge diameter</b>   | 20 mm            |
| <b>Clearance length</b>        | 30 mm            |
| <b>Length</b>                  | 30 mm            |
| <b>Thread dimension</b>        | M10              |
| <b>max. ap</b>                 | 5.5 mm           |
| <b>Number of cutting edges</b> | 5 PCS            |

### EAN-Code

4050293637328

