

Product Information Sheet

COMMISSION DELEGATED REGULATION (EU) 2019/2015 with regard to energy labelling of light sources

Supplier's name or trade mark: Sun Cracks

Supplier's address: -

Model identifier: 101603

Type of light source:

Lighting technology used:	LED	Non-directional or directional:	DLS
Light source cap-type (or other electric interface)	Nicht austauschbare Lichtquelle		
Mains or non-mains:	MLS	Connected light source (CLS):	Nein
Colour-tuneable light source:	Nein	Envelope:	-
High luminance light source:	Nein		
Anti-glare shield:	Nein	Dimmable:	No

Product parameters

Parameter	Value	Parameter	Value
General product parameters:			
Energy consumption in on-mode (kWh/1000 h), rounded up to the nearest integer	35	Energy efficiency class	D
Useful luminous flux (ϕ_{use}), indicating if it refers to the flux in a sphere (360°), in a wide cone (120°) or in a narrow cone (90°)	3 720 in Narrow cone (90°)	Correlated colour temperature, rounded to the nearest 100 K, or the range of correlated colour temperatures, rounded to the nearest 100 K, that can be set	4 000
On-mode power (P_{on}), expressed in W	35,0	Standby power (P_{sb}), expressed in W and rounded to the second decimal	0,00
Networked standby power (P_{net}) for CLS, expressed in W and rounded to the second decimal	-	Colour rendering index, rounded to the nearest integer, or the range of CRI-values that can be set	92
Outer dimensions	Height	Spectral power distribution in the	See image in last page
	Width		
			100

without separate control gear, lighting control parts and non-lighting control parts, if any (millimetre)	Depth	100	range 250 nm to 800 nm, at full-load	
Claim of equivalent power ^(a)		-	If yes, equivalent power (W)	-
			Chromaticity coordinates (x and y)	0,388 0,384
Parameters for directional light sources:				
Peak luminous intensity (cd)		-	Beam angle in degrees, or the range of beam angles that can be set	60
Parameters for LED and OLED light sources:				
R9 colour rendering index value		57	Survival factor	-
the lumen maintenance factor		-		
Parameters for LED and OLED mains light sources:				
displacement factor (cos ϕ_1)		0,95	Colour consistency in McAdam ellipses	-
Claims that an LED light source replaces a fluorescent light source without integrated ballast of a particular wattage.		-(b)	If yes then replacement claim (W)	-
Flicker metric (Pst LM)		-	Stroboscopic effect metric (SVM)	-

(a)-: not applicable;

(b)-: not applicable;