


PF0033/15/63 Datasheet

Product Name // IEC Connector Snap Fit To Panel Twin Fused Inlet PF0033 Series 1.5mm Panel 6.3mm Tab Termination EN60 320-1 Standard Sheet C14 Class I

[View Product Page](#)



// Product Description:

- ⊗ Snap Fit Panel Mount Twin Fused IEC Inlets
- ⊗ EN60 320-1 Standard Sheet C14 Class I
- ⊗ Twin Fused, 5mm x 20mm fuses
- ⊗ Choice of panel thickness depending on part code: /10 - 1mm, /15 - 1.5mm, /20 - 2mm, /30 - 3mm
- ⊗ Choice of Termination depending on part code: /28 - 2.8mm Solder Tag, /48 - 4.8mm Tab, /63 - 6.3mm Tab
- ⊗ Insulation Boot for rear of connector available separately (part code 14317)
- ⊗ Mate with PX0587, PX0587/SE, PX0588

// General Information:

Product Configurator:	No
Product Display Title:	Snap Fit Panel Mount Twin Fused IEC Inlets
Product Family:	IEC Connectors
Product Series:	IEC60320 Main Inlets and Outlets
Pdfbuilder Enabled:	Yes
Weight:	0.022
Product Technical Image:	pf00331028_diagram.jpg
Technical Image:	pf00331028_diagram.jpg
Approvals:	CSA, UL
Body Material:	Nylon 66
Current Max:	10A
Flamability Rating:	UL94V-0
Function:	Panel Mount Fused Connector
iec Connector Mates With:	PX0587,PX0587/SE,PX0588
iec En60620 Type:	EN60 320-1 Standard Sheet C14 Class I
Max Operating Temperature:	+70°C
Min Operating Temperature:	-20°C
Max Panel Thickness:	1.5mm
Min Panel Thickness:	1.5mm
Number Of Contacts:	3 Contacts
Rohs Compliant:	Yes
Voltage Max:	250V
Package Id:	564

// Product PDF Links

[IEC Connectors product data](#)

// Product 3D CAD Model Links

[PF0033/15/633D CAD Model](#)