

# HUBER+SUHNER® DATA SHEET

## Within Series Adapter: 53\_BNC-75-0-1/133\_N

Rev.: A 

### Description

L-adaptor plug/jack

Interface standards  
IEC 60169-8\_MIL-STD-348A/301\_CECC 22120



### Technical Data

#### Electrical Data

Impedance 75  $\Omega$   
Interface frequency max. 1 GHz

#### Mechanical Data

Weight 0.0154 kg

#### Environmental Data

Operating Temperature -65 °C to 165 °C  
2002/95/EC (RoHS) compliant

#### Material Data

##### Piece Parts

Centre contact	Copper Beryllium / Brass
Outer contact	Brass
Body	Brass
Insulator	PFA / PTFE
Coupling nut	Brass
Gasket	MVQ (Silicone Rubber)

##### Surface Plating

Gold Plating (Nickel underplated)
SUCOPLATE (R) Plating
SUCOPLATE (R) Plating
SUCOPLATE (R) Plating

#### Related Documents

Catalogue drawing DCA-00013460

#### Ordering Information

Single package 53\_BNC-75-0-1/133\_NE

HUBER+SUHNER is certified according to ISO 9001 and ISO 14001

#### WAIVER!

It is exclusively in written agreements that we provide our customers with warrants and representations as to the technical contained specifications and/or the fitness for any particular purpose. The facts and figures herein are carefully compiled to the best of our knowledge, but they are intended for general informational purposes only.



**HUBER+SUHNER AG**  
RF Technology  
9100 Herisau, Switzerland  
Phone +41 (0)71 353 41 11  
Fax +41 (0)71 353 45 90  
www.hubersuhner.com

**HUBER+SUHNER – Excellence in Connectivity Solutions**