

AS-I CABLE TRAPEZOIDAL YELLOW, TPE, OIL-RESISTANT, 2 X 1,5QMM, 100M 1 PIECE = 100M



Figure similar

General technical data:		
Design of the product		AS-Interface shaped cables
Colour		yellow (AS-Interface)
Material		TPE
Quantity		100 m roll
Mechanical data:		
Without silicone precipitation		yes
bending radius according to DIN VDE 0298 Part 300		
• fixed min	m	12
• freely movable min	m	24
Without halogens		no
Flexibility		good
Bending behavior according according to DIN VDE 0472 Part 603		no break after 30000 reverse bending cycles
Core colours		brown, blue
Ambient conditions:		
Fire behavior		flame-retardant according to IEC 60332-1;VDE 0482 T. 265-2-1;UL 1581 sec. 1061 cable flame;UL 1581 sec. 1060 CSA FT1
resistance to oil		resistant
Ozone and weather resistant		resistant
Temperature range		
• stationary	°C	-40 ... +105
• moved	°C	-30 ... +105

Certificates/ approvals:

Approvals Canada	CSA	C22.2 No.210.2 AWM
Approvals USA	UL	UL 758 AWM
Monitored expertise (VDE)		no

General Product Approval	Shipping Approval	other
--------------------------	-------------------	-------



[Declaration of Conformity](#)

[Environmental Confirmations](#)

Further information

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/industrial-controls/catalogs>

Industry Mall (Online ordering system)

<http://www.siemens.com/industrymall>

Cax online generator

<http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3RX90130AA00>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<http://support.automation.siemens.com/WW/view/en/3RX90130AA00/all>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

<http://www.automation.siemens.com/bilddb/index.aspx?attID9=3RX90130AA00&lang=en>

last modified:

09.03.2015