
### **Solid State Relay**

## multicomp PRO

### RoHS Compliant



### Description

The product is single channel din-rail mounted module with 5A. Control voltage is 15-32V DC and isolation voltage is 4000V ACrms with high EMC capability, high inrush current, special for automatic machinery, control system, elevator, entertainment equipment.

### Features

- Load Current: 0.1A to 5A
- Din Rail Mounted
- DC Control
- LED Indication
- High EMC Capability
- High Inrush Current

### Application

Suitable for Automatic Equipment, Control System, Entertainment Equipment.

### **Technical Specification**

#### **Input Circuit**


Control Voltage Range Min. Turn-On Voltage Min. Turn-Off Voltage Max. Input Current	: 15V DC to 32V DC : 15V DC : 1V DC : 25mA
Output Circuit	
Load Voltage Range	: 48V AC to 280V AC
Transient Overvoltage	: 600Vpk
Load Current Range	: 0.1A to 5A
Max. Turn-On Time	: 1/2AC Cycle + 1ms
Max. Surge Current (@10 ms)	: 60A
Max. Off-State Leakage Current [@ Rated Voltage]	: 5mA
Max. On-State Voltage Drop [@ Rated Current]	: 1.5Vrms
Min. Off-State dv/dt [ @ Max. Rated Voltage]	: 200V/µs
General Information	
Dielectric Strength Input/Output	: ≧4000Vrms
Ambient Operating Temperature Range	: -30°C to +80°C
Ambient Storage Temperature Range	: -30°C to +100°C
Weight (Typical)	: 55g

Newark.com/multicomp-pro Farnell.com/multicomp-pro Element14.com/multicomp-pro

### multicomp PRO

# multicomp PRO


### Diagram



### Wiring Diagram




### Thermal Curve



### Part Number Explanation





-KSD240D5

Control Voltage H: 15-32V DC

-H(037)

### Part Number Table

Description	Part Number
Solid State Relay, Din module, 280V AC, 5A, 15-32V DC	MCDRA-1/KSD240D5-H(037)

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for white any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro Farnell.com/multicomp-pro Element14.com/multicomp-pro

