

Type: **DILM50(230V50HZ,240V60HZ)**

Article No.: **277830**



Ordering information

| | | | |
|---|----------------|----|---------------------------------------|
| Rated operational current AC-3 400 V | I_e | A | 50 |
| Max. rating for three-phase motors, 50 – 60 Hz AC-3 230 V | P | kW | 15.5 |
| Max. rating for three-phase motors, 50 – 60 Hz AC-3 400 V | P | kW | 22 |
| Max. rating for three-phase motors, 50 – 60 Hz AC-3 690 V | P | kW | 30 |
| Max. rating for three-phase motors, 50 – 60 Hz AC-4 230 V | P | kW | 6 |
| Max. rating for three-phase motors, 50 – 60 Hz AC-4 400 V | P | kW | 10 |
| Max. rating for three-phase motors, 50 – 60 Hz AC-4 690 V | P | kW | 14 |
| Conventional thermal current $I_{th} = I_e$ AC-1 Open | $I_{th} = I_e$ | A | 60 |
| For use with | | | DILM150-XHI(V).. DILM1000-XHI(V).. |

General

| | | | |
|---------------------------------|--------------|---------------|--|
| Standards | | | IEC/EN 60947, VDE 0660, UL, CSA |
| Lifespan, mechanical | | | |
| AC operated | Operations | $\times 10^6$ | 10 |
| DC operated | Operations | $\times 10^6$ | 10 |
| Operating frequency, mechanical | | | |
| AC operated | Operations/h | | 5000 |
| DC operated | Operations/h | | 5000 |
| Climatic proofing | | | Damp heat, constant, to IEC 60068-2-78 Damp heat, cyclical, to IEC 60068-2-30 |
| Ambient temperature | | | |

| | | | |
|--|--|-----------------|--------------------------------------|
| Open | | °C | -25/60 |
| Enclosed | | °C | -25/40 |
| Storage | | °C | -40/80 |
| Mechanical shock resistance (IEC/EN 60068-2-27) | | | |
| Half-sinusoidal shock, 20 ms | | | |
| Main contacts | | | |
| Make contact | | g | 10 |
| Auxiliary contacts | | | |
| Make contact | | g | 7 |
| Break contact | | g | 5 |
| Protection type | | | IP00 |
| Protection against direct contact when actuated from front (IEC 536) | | | Finger- and back-of-hand proof |
| Weight | | | |
| AC operated | | kg | 0,9 |
| DC operated | | kg | 1,1 |
| Terminal capacity Main cable | | | |
| Solid | | mm ² | 1 × (2.5 – 16) 2 × (2.5 – 16) |
| Flexible with ferrule | | mm ² | 2 × (2.5 – 25) 1 × (2.5 – 35) |
| Stranded | | mm ² | 1 × (16 – 50) 2 × (16 – 35) |
| Solid or stranded | | AWG | 12 – 2 |
| flat conductor | Number of segments × width × thickness | mm | 2 × (6 × 9 × 0.8) |
| Anschlussschraube Hauptleiter | | | M6 |
| Tightening torque | | Nm | 3 |
| Terminal capacity Control circuit cables | | | |
| Solid | | mm ² | 1 × (0.75 – 4) 1 × (0.75 – 4) |
| Flexible with ferrule | | mm ² | 1 × (0.75 – 2.5) 2 × (0.75 – 2.5) |
| Solid or stranded | | AWG | 18 – 14 |
| Anschlussschraube Hilfsleiter | | | M3.5 |
| Tightening torque | | Nm | 1.2 |
| Tool | | | |
| Main cable | | | |
| Pozidriv screwdriver | | Size | 2 |
| Standard screwdriver | | mm | 0.8 × 5.5 1 × 6 |
| Control circuit cables | | | |
| Pozidriv screwdriver | | Size | 2 |
| Standard screwdriver | | mm | 0.8 × 5.5 1 × 6 |
| Terminal capacity Control circuit cables | | | |
| Solid | | mm ² | 0.75 – 2.5 |

| | | | |
|-------------------------|--|-----------------|------------|
| Flexible | | mm ² | 0.75 – 2.5 |
| Flexible with ferrule | | mm ² | 0.75 – 2.5 |
| Solid or stranded | | AWG | 18 – 14 |
| Tool | | | |
| Stripping length | | mm | 10 |
| Screwdriver blade width | | mm | 3,5 |

Main conducting paths

| | | | |
|---|-------------|-------|--------------------------|
| Rated impulse withstand voltage | U_{imp} | V AC | 8000 |
| Overvoltage category/pollution degree | | | III/3 |
| Rated insulation voltage | | | |
| AC | U_i | V AC | 690 |
| Rated operational voltage | U_e | V AC | 690 |
| Safe isolation to VDE 0106 Part 101 and Part 101/A1 | | | |
| between coil and contacts | | V AC | 440 |
| between the contacts | | V AC | 440 |
| Making capacity (cos \tilde{O} to IEC/EN 60947) up to 690 V | | A | 700 |
| Breaking capacity | | | |
| 220/230 V | | A | 500 |
| 380/400 V | | A | 500 |
| 500 V | | A | 500 |
| 660/690 V | | A | 320 |
| Component lifespan | | | |
| AC–3/AC–4 | | | Tripping characteristics |
| Maximum operating frequency | | | |
| AC–1; 400 V | I_e | Ops/h | 800 |
| AC–3; 400 V | I_e | Ops/h | 800 |
| AC–4; 400 V | I_e | Ops/h | 300 |
| Short–circuit rating | | | |
| Short–circuit protection Maximum fuse | | | |
| Type “2” coordination | | | |
| 400 V | gG/gL 500 V | A | 80 |
| 690 V | gG/gL 690 V | A | 63 |
| Type “1” coordination | | | |
| 400 V | gG/gL 500 V | A | 160 |
| 690 V | gG/gL 690 V | A | 80 |


AC

| | | | |
|--|----------|---|----|
| AC–1 duty | | | |
| conv. therm. current 3–pole 50 – 60 Hz | | | |
| open | | | |
| at 40 °C | I_{th} | A | 70 |
| at 50 °C | I_{th} | A | 65 |
| at 55 °C | I_{th} | A | 63 |
| at 60 °C | I_{th} | A | 60 |
| Enclosed | I_{th} | A | 54 |

| | | | |
|---|----------|----|------|
| Conventional free air thermal current, 1-pole | | | |
| open | I_{th} | A | 150 |
| Enclosed | I_{th} | A | 135 |
| AC-3 duty | | | |
| Rated operational current AC-3 open, 50 – 60 Hz, 3-pole | | | |
| 220/230 V | I_e | A | 50 |
| 240 V | I_e | A | 50 |
| 380/400 V | I_e | A | 50 |
| 415 V | I_e | A | 50 |
| 440V | I_e | A | 50 |
| 500 V | I_e | A | 50 |
| 660/690 V | I_e | A | 32 |
| Motor rating | | | |
| 220/230 V | P | kW | 15,5 |
| 240V | P | kW | 17 |
| 380/400 V | P | kW | 22 |
| 415 V | P | kW | 30 |
| 440 V | P | kW | 32 |
| 500 V | P | kW | 36 |
| 660/690 V | P | kW | 30 |
| AC-4 duty | | | |
| Rated operational current AC-4 open, 50 – 60 Hz, 3-pole | | | |
| 220/230 V | I_e | A | 21 |
| 240 V | I_e | A | 21 |
| 380/400 V | I_e | A | 21 |
| 415 V | I_e | A | 21 |
| 440 V | I_e | A | 21 |
| 500 V | I_e | A | 21 |
| 660/690 V | I_e | A | 17 |
| Motor rating | | | |
| 220/230 V | P | kW | 6 |
| 240 V | P | kW | 6,5 |
| 380/400 V | P | kW | 10 |
| 415 V | P | kW | 11 |
| 440 V | P | kW | 12 |
| 500 V | P | kW | 13 |
| 660/690 V | P | kW | 14 |
| DC | | | |
| of three-phase capacitors open | | | |
| DC-1 operation | | | |
| 60 V | I_e | A | 60 |
| 110 V | I_e | A | 50 |
| 220 V | I_e | A | 45 |
| 440 V | I_e | A | 2,9 |
| DC-3 operation | | | |

| | | | |
|--|---------|--------------|---------------|
| 60 V | I_e | A | 60 |
| 110 V | I_e | A | 50 |
| 220 V | I_e | A | 25 |
| 440 V | I_e | A | 0,6 |
| DC-5 operation | | | |
| 60 V | I_e | A | 60 |
| 110 V | I_e | A | 50 |
| 220 V | I_e | A | 25 |
| 440 V | I_e | A | 0,6 |
| Current heat loss (3-pole) | | | |
| Current heat loss at I_{th} | | W | 16,2 |
| Current heat loss at I_e to AC-3/400 V | | W | 11,3 |
| Impedance per pole | | mΩ | 1,5 |
| Magnet systems | | | |
| Voltage tolerance | | | |
| AC operated | | | |
| AC operated | Pick-up | $\times U_c$ | 0,8 – 1,1 |
| Drop-out voltage AC operated | | | |
| Drop-out voltage AC operated | Abfall | $\times U_c$ | 0,3 – 0,6 |
| DC operated | | | |
| DC operated | Pick-up | $\times U_c$ | 0,7 – 1,2 |
| DC operated | | | |
| DC operated | Abfall | $\times U_c$ | 0,15–0,6 |
| Power consumption of the coil in a cold state and $1.0 \times U_c$ | | | |
| 50 Hz | Pick-up | VA | 130 |
| 50 Hz | Pick-up | W | 80 |
| 50 Hz | Sealing | VA | 14 |
| 50 Hz | Sealing | W | 4 |
| DC operated | Pick-up | W | 24 at 24 V |
| DC operated | Sealing | W | 0.5 at 24 V |
| Duty factor | | % DF | 100 |
| Switching times at 100 % U_c (approximate values) | | | |
| Main contacts | | | |
| AC operated | | | |
| Closing delay | | ms | 25 |
| Opening delay | | ms | 25 |
| DC operated | | | |
| Closing delay | | ms | 60 |
| Opening delay | | ms | 20 |
| Arcing time | | ms | 10 |
| Electromagnetic compatibility (EMC) | | | |
| Emitted interference | | | to EN 60947-1 |
| Interference immunity | | | to EN 60947-1 |

Mounting position, AC- and DC operated



Moeller GmbH, Hein-Moeller-Str. 7-11, D-53115 Bonn
E-Mail: catalog@moeller.net, Internet: www.moeller.net, <http://catalog.moeller.net>
Copyright 2005 by Moeller GmbH. Subject to modifications. HPL-C2005GB-INT V3.0