

## Centre drill HSSE, type A, with face

For universal use up to 1000 N/mm<sup>2</sup>

**ATORN**<sup>®</sup>



### Application

For centre drilling on conventional and CNC machines.

### Version

- spiral-fluted design with relief grinding

### Advantage

- Face ensures good accessibility
- radial relief ensures optimum chip breaking

Application	Steel (N/mm <sup>2</sup> )			Stainless steel		Alu		Brass		Bronze		Plastics	Graphite G(C)FK	GG(G) GJMW	Titan-alloy	Nickel-alloy	Super-alloy	Hard mat.	
	<700	<1000	<1300	marten.	austen.	short	long	short	long	short	long							<55 HRC	<65 HRC
	40	20	20	15	10	50	80	40	30	35	40	20	10	20	5	5	5		

<b>Art. No.</b>	<b>11001 160</b>
<b>Countersink angle</b>	60 Degree
<b>Cutting material</b>	HSSE
<b>Surface</b>	Uncoated
<b>Form</b>	A
<b>Tool holding device</b>	HA parallel shank
<b>Cutting edge diameter</b>	1.60 mm
<b>Shaft diameter</b>	4 mm
<b>Min./max cutting edge length</b>	2-2.6 mm
<b>Length</b>	35 mm
<b>f steel 700</b>	0.03 mm/U
<b>DIN</b>	333

### EAN-Code

4050293415032