

## RF Attenuator 6610\_SMA-50-2/199\_N

### Description

Standard Attenuator, Low Power



### Product Configuration

Connector (side 1 / side 2) SMA plug (male) / SMA jack (female)  
Interface Standards IEC 60169-15\_MIL-STD-348A/310\_CECC 22110

### Technical Data

#### Electrical Data

Nominal impedance 50 Ω  
Nominal attenuation 10 dB  
Frequency range DC to 6 GHz  
Attenuation deviation (±dB) 0.6  
VSWR max. 1.2  
Power rating 2 Watt average power up to 25 °C ambient temperature, linearly derated to 1.1 Watt at 85 °C ambient temperature.

#### Mechanical Data

Weight 0.004 kg

#### Environmental Data

Operating temperature -20 °C to 85 °C  
2011/65/EU (RoHS - including 2015/863 and 2017/2102) compliant

#### Material Data

Piece Part (side 1)	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	Gold Plating
Outer contact	Stainless Steel	Passivated (Plating)
Body	Stainless Steel	Passivated (Plating)
Insulator	PTFE (Polytetrafluoroethylene)	
Coupling nut	Stainless Steel	Passivated (Plating)
Piece Part (side2)	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	Gold Plating
Outer contact	Stainless Steel	Passivated (Plating)
Body	Stainless Steel	Passivated (Plating)
Insulator	PTFE (Polytetrafluoroethylene)	

### Related Documents

Outline drawing DOU-00089026

### Ordering Information

Single packaging 6610\_SMA-50-2/199\_NE