

## Boring bar holder type E2



### Application:

For clamping boring bars on lathes.

### Execution:

- For NC lathes
- For external and internal coolant supply
- Burnished
- tool chucks in accordance with DIN 69880/VDI 3425



<b>Art. no.</b>	<b>22770 316</b>
<b>Brand</b>	EWS
<b>Manufacturer Part Number</b>	135654
<b>VDI mount diameter</b>	30
<b>Clamping diameter</b>	16 mm
<b>Outer diameter</b>	68 mm
<b>Projecting length</b>	60 mm
<b>Coolant supply</b>	Yes
<b>Gross Weight</b>	1.337 kg
<b>Product Group</b>	215