

Suspended wall cabinet with 2 solid sheet metal doors

With smooth rear wall

Application:

For stowing away tools or other parts in a clearly-arranged and space-saving manner directly on or above workstations.

Execution:

- Robustly welded steel sheet design
- 2 holes in the rear wall for wall mounting
- 1 powder-coated shelf, height-adjustable in the grid by 17 mm, incl. 4 shelf supports, load capacity of 15 kg when load evenly distributed
- With two hinged doors
- Internal doors reinforced with box profiles, inset-type with internal pivot pins, approx. 125° door opening angle
- Lockable with cylinder lock, incl. 2 keys
- Overall load capacity of the cabinet 30 kg with evenly distributed load

Delivery:

Without fastening material



| | |
|---|--------------------------|
| Art. no. | 50045 123 |
| Brand | PAVOY |
| Manufacturer Part Number | 22337-080-001-735716 |
| Door design | Full-sheet panel |
| Width | 800 mm |
| Depth | 300 mm |
| Height | 600 mm |
| Number of shelves | 1 PCS |
| Load-carrying capacity per shelf | 15 kg |
| Back panel design | Smooth |
| Central locking | Yes |
| Lock type | Cylinder lock |
| Load-carrying capacity | 30 kg |
| Material | Sheet steel |
| Cabinet colour | Light grey RAL 7035 |
| Colour of front | Anthracite grey RAL 7016 |
| Surface | Powder-coated |
| Gross Weight | 15.000 kg |
| Product Group | 5CB |