


# SM6004

## Magnetic-inductive flow meter

SMR12GGX50KG/US-100



### Product characteristics

Number of inputs and outputs	Number of analogue outputs: 2	
Measuring range	0.1...25 l/min	0.03...6.6 gpm
Process connection	threaded connection G 1/2 DN15 flat seal	

### Application

Special feature	Gold-plated contacts
Application	for industrial applications
Installation	connection to pipe by means of an adapter
Media	conductive liquids; water; hydrous media
Note on media	conductivity: $\geq 20 \mu\text{S}/\text{cm}$ viscosity: $< 70 \text{ mm}^2/\text{s}$ (40 °C)
Medium temperature [°C]	-10...70
Pressure rating [bar]	16
MAWP (for applications according to CRN) [bar]	17.7

### Electrical data

Operating voltage [V]	20...30 DC; (according to EN 50178 SELV/PELV)
Current consumption [mA]	120; (24 V)
Protection class	III
Reverse polarity protection	yes
Power-on delay time [s]	5

### Inputs / outputs

Number of inputs and outputs	Number of analogue outputs: 2
------------------------------	-------------------------------

# SM6004



## Magnetic-inductive flow meter

SMR12GGX50KG/US-100

### Outputs

Total number of outputs		2
Output signal		analogue signal
Number of analogue outputs		2
Analogue current output	[mA]	4...20; (scalable)
Max. load	[Ω]	500
Overload protection		yes

### Measuring/setting range

Measuring range		0.1...25 l/min	0.03...6.6 gpm
Display range		-30...30 l/min	-7.92...7.92 gpm
Resolution		0.02 l/min	0.01 gpm
Analogue start point ASP		0...20 l/min	0...5.28 gpm
Analogue end point AEP		5...25 l/min	1.32...6.6 gpm
In steps of		0.02 l/min	0.01 gpm

### Temperature monitoring

Measuring range	[°C]	-20...80
Resolution	[°C]	0.2
Analogue start point	[°C]	-20...60
Analogue end point	[°C]	0...80
In steps of	[°C]	0.2

### Accuracy / deviations

Flow monitoring		
Accuracy (in the measuring range)	± (2 % MW + 0,5 % MEW)	
Repeatability	± 0,2% MEW	
Temperature monitoring		
Accuracy	[K]	± 2,5 (Q > 1 l/min)

### Response times

Flow monitoring		
Response time	[s]	0.15; (dAP = 0, T19)
Damping for the switching output dAP	[s]	0...3
Temperature monitoring		
Dynamic response T05 / T09	[s]	T09 = 20 (Q > 1 l/min)

### Operating conditions

Ambient temperature	[°C]	-10...60
Storage temperature	[°C]	-25...80
Protection		IP 67

### Tests / approvals

EMC	DIN EN 60947-5-9	500 V withstand voltage (V DC)
Shock resistance	DIN IEC 68-2-27	20 g (11 ms)
Vibration resistance	DIN IEC 68-2-6	5 g (10...2000 Hz)
MTTF	[years]	175
Pressure Equipment Directive		Sound engineering practice; can be used for group 2 fluids; group 1 fluids on request

# SM6004

## Magnetic-inductive flow meter

SMR12GGX50KG/US-100




Mechanical data		
Weight	[g]	516.5
Materials		stainless steel (1.4404 / 316L); PBT-GF20; PC; FKM; TPE
Materials (wetted parts)		stainless steel (1.4404 / 316L); PEEK; FKM
Process connection		threaded connection G 1/2 DN15 flat seal
Displays / operating elements		
Display	Display unit measured values programming	6 x LED, green (l/min, m³/h, gpm, gph, °C, °F) alphanumeric display, 4-digit alphanumeric display, 4-digit
Display unit		l/min; m³/h; gpm; gph; °C; °F
Remarks		
Remarks		MW = measured value MEW = Final value of the measuring range
Pack quantity		1 pcs.
Electrical connection		
Connector: 1 x M12; Contacts: gold-plated		



## Magnetic-inductive flow meter

SMR12GGX50KG/US-100

### Connection



colours to DIN EN 60947-5-2

OUT1: analogue output Temperature monitoring

OUT2: analogue output volumetric flow quantity monitoring

Core colours :

BK = black


BN = brown

BU = blue

WH = white

### Diagrams and graphs

Pressure loss



dP Pressure loss

Q volumetric flow quantity