Delay On Operate, Multi-voltage Timer



Terminal Protection to IP20


Dims: to DIN 43880

- *NEW* 17.5mm DIN rail housing
- Supply Initiated Delay On Operate timing function
- □ 7 Selectable time ranges (0.1 seconds 100 hours)
- □ Fine adjustment of selected time range
- Multi-voltage input (12 230V AC/DC)
- 1 x SPDT relay output 8A
- □ Green LED indication for supply / timing status

Installation work must be carried out by qualified personnel.

- □ Red LED indication for relay status
- □ Conforms to IEC 61812





INSTALLATION AND SETTING

- BEFORE INSTALLATION, ISOLATE THE SUPPLY.
- Connect the unit as required.

Setting the unit.

- Set the "Range" 4 to the required position (depending on whether seconds, minutes or hours are required).
- Set the "Set %" adjustment ❸ as required. The "Set %" is a % of the selected range; so for example, a 30% setting on the 1 10 hour range will give 3 hours.


Applying power.


- Apply power across terminals "A1" and "A2" and the green LED
 will start flashing indicating timing in progress
- The relay will remain de-energised (contacts 15 / 16 closed and 15 / 18 open) and red LED @ extinguished.
- After the delay period "t" has elapsed, the relay will energise (contacts 15 / 16 open and 15 / 18 closed) and the red LED will illuminate.
- The green LED will remain permanently lit.
- The whole timing process is repeated by removing and re-applying power.

Note:

¹ In accordance with IEC 61812, the green LED is permitted to extinguish during a voltage dip or momentary interruption of the power supply providing the state of the output relay does not change. The dip / interruption duration and levels are defined in the product standard.

Supply voltage U (A1, A2):		12 – 230V AC/DC				
Frequency range:		48 - 63Hz (AC supplies)				
Supply variation:		+/ - 15%				
Overvoltage category:		III (IEC 60664)				
Rated impulse withstand voltage:		4kV (1.2/50μS) IEC 60664				
Power consumption (max.):		12V	24V	110V	230V	
	AC:	0.3VA	0.4VA	1.3VA	3.4VA	
	DC:	0.26W	0.24W	0.47W	0.95W	
Timing function:		Delay On Operate (Supply Initiated)				
Timing ranges (7):		Seconds:	Minut	es:	Hours:	
		0.1 - 1	0.1 - 1	l	0.1 - 1	
		1-10	1-10		1-10	
					10 - 100	
Reset time:		100mS				
Accuracy:		± 1% of maximum full scale				
Adjustment accuracy:		< 5% of maximum full scale				
Repeat accuracy:		\pm 0.5% at constant conditions (IEC 61812)				
Drift with temperature:		± 0.05% / °C				
Drift with voltage:		± 0.2% / V				
Power on indication / Timing ¹ :		Green LED				
Relay status		Red LED				
Ambient temp:		-20 to +60°C				
Relative humidity:		+95%				
Output (15, 16, 18):		SPDT relay				
Output rating:		AC1		250V 8	250V 8A (2000VA)	
		AC15	AC15		250V 5A (no), 3A (nc)	
		DC1	DC1 25V 8A (200W)			
Electrical life:		≥ 150,000 ops at rated load				
Dielectric voltage:		2kV AC (rms) IEC 60947-1				
Rated impulse withstand voltage:		4kV (1.2/50μS) IEC 60664				
Housing:		Orange flame retardant UL94				
Weight:		≈ 60g				
Mounting option:		On to 35mm symmetric DIN rail to BS EN 60715 or direct surface mounting via 2 x M3.5 or 4BA screws using the black clips provided on the rear of the unit.				
Terminal conductor size		≤ 2 x 2.5mm ² solid or stranded				
Approvals:		Conforms	to IEC 61812.			





CE, C-tick Cand RoHS Compliant.

80MHz - 2.7GHz)

Emissions: EN 61000-6-4

EMC: Immunity: EN 61000-6-2 (EN 61000-4-3 10V/m