

Electronics end cutting nippers ESD

End-cutting nippers, with small chamfer



Application:

For precision cutting tasks in electronics and precision mechanics fields.

Execution:

- Ball bearing chrome steel
- Blades also inductively hardened
- Pushed-through precision joint
- Low-friction double spring for smooth, even opening action

Advantage:

- Mirror-finished surface with fine oil film to protect against rust, no interference in the circuit by flaking chrome parts
- Safe, ergonomic and fatigue-free working thanks to two-component handles
- ESD design, discharges electricity



Art. no.	53105 060
Brand	KNIPEX
Manufacturer Part Number	64 12 115 ESD
Length	115 mm
Max. soft wire diameter cutting capacity	1.4 mm
Head design	Without bevel
Surface	Plain
Material of handle	2-component plastic
ESD-capable	Yes
Gross Weight	0.089 kg
Product Group	535

EAN

4003773024323