




## Fibre optic through beam sensor

FE-11-EPA-Q-/F16X0,265



1 light emission

Application		
Design		Cross section converter
Function principle		Through-beam sensor
Detection zone		
Range with fibre optic amplifier type		OB50; OBF; OO50
OB50		
Range of fibre optics	[mm]	150
OBF		
Range of fibre optics	[mm]	300
OO50		
Range of fibre optics	[mm]	700
Operating conditions		
Ambient temperature	[°C]	-40...70
Mechanical data		
Weight	[g]	61
Sensing head height	[mm]	5
Sensing head width	[mm]	20
Sensing head length	[mm]	20
Sensing head length	[mm]	5 x 20 x 20
Total length	[mm]	2000
Min. bending radius	[mm]	9
Fibre arrangement		⏏
Core diameter	[mm]	16 x 0.25
Fibre material		PMMA
Fibre head material		aluminium
Fibre sheath material		PE
Accessories		
Accessories (optional)		Cutter for fibre optics, E20600

# E20757



## Fibre optic through beam sensor

FE-11-EPA-Q-/F16X0,265

### Remarks

Pack quantity	1 pcs.
---------------	--------