

## Wire end brushes with crimped stranded wire

Shaft diameter 6 mm, for use on fast-running machines

**ATORN**<sup>®</sup>

### Application

For roughening, deburring, stripping paint or removing burrs, rust and combustion residues in hard-to-reach places in steel machining.

### Version

- 3-4 brass-plated steel wires with single wire diameters of 0.2 mm twisted into rope construction
- Spring hard and tough



<b>Art. No.</b>	<b>76097 171</b>
<b>Head diameter</b>	16 mm
<b>Length of bristles</b>	25 mm
<b>Shaft diameter</b>	6 mm
<b>Material to be processed</b>	Steel, Wood
<b>Length</b>	45 mm
<b>Wire diameter</b>	0.20 mm
<b>Max. rotation speed</b>	20000 U/min(rpm)
<b>Number of pieces per packet</b>	5 PCS
<b>Edging material</b>	Steel

### EAN-Code

4050293317664