

FS2250 SERIES WORLD CLASS VERTICAL FIRE FILE



FS2254E



FS2252K



Data protection insert (FSDPI08)

FS2250 Series = 25 inch deep



FS2250F

THE PHOENIX WORLD CLASS VERTICAL FIRE FILE series offers unrivalled protection for documents and data† in a stylish modern filing cabinet format. Ultra lightweight insulation materials mean the cabinet can be used on most floors without the need for supporting.

- **FIRE PROTECTION (PAPER)** – 90 minutes fire protection for paper documents.
- **FIRE PROTECTION (DATA)** – 90 minutes fire protection for Computer tapes and data if optional FSDPI08 is used.
- **FIRE PROTECTION (DIGITAL MEDIA)** – Tested to MTC DIP120-60DM fire test standard, providing 60 minutes fire protection for digital media, USB's, memory sticks and hard drives.
- **WATER RESISTANCE** – Water resistant seals prevent water damage to contents when cabinet is subjected to sprinklers systems or fire hoses.***
- **DROP TEST** – Fire and impact tested from 9.1 metres for resistance to the impact of falling through the burning floors of a building.
- **LOCKING – FS2250K** – Fitted with a high quality key lock supplied with two keys. **FS2250E** – Fitted with an advanced high security electronic lock with clear LED display, dual control, hidden code & scrambled code that can be programmed as standard.

FS2250F – Fitted with an advanced high security touchscreen keypad & fingerprint lock with clear LED display, internal alarm, dual control, hidden code and scrambled code that can be programmed as standard with up to 128 fingerprints.

- **CAPACITY** – Able to accommodate Foolscap, A4 and A5 files on width adjustable rails. Compression plates are also supplied to maximise useable space.
- **COLOUR** – Finished in a high quality scratch resistant white paint RAL9003.
- **GDPR** – Maintain GDPR Compliance at home or in the office by keeping your company's vital and important records secure and protected.

MODEL NUMBER	EXTERNAL DIMENSIONS H x W x D	INTERNAL DIMENSIONS H x W x D	WEIGHT	CAPACITY PER DRAWER	TOTAL CAPACITY	DRAWERS
FS2252K/E/F	720 x 530 x 675mm	255 x 385 x 505mm**	140kg	49 Litres	98 Litres	2
FS2254K/E/F	1405 x 530 x 675mm	255 x 385 x 505mm**	266kg	49 Litres	196 Litres	4
Data Protection Insert – FSDPI08 (FS2250 only)						
	260 x 380 x 500mm	165 x 282 x 402mm	20kg	19 Litres	-	



*** Does not protect against water submersion ** Internal dimensions for the drawers † When using Phoenix FSDPI08

