## **High Isolation Power Transformers**

Toroid Platform SMD






- 🦻 Push Pull Converter Transformer
- 🔗 4KVrms Isolation
- 🕐 Reinforced insulation, 9.5mm Creepage
  - **9** Sidecar Package
  - **Patented:** US Pat 9,646,755

Electrical Specifications @ 25°C – Operating Temperature –40°C to +125°C										
Part Number	<b>Inductance</b> (1-3) (μH ±35%)	Leakage Inductance (1-3) with (4-6) shorted (µH MAX)	<b>Capacitance</b> (1, 2, 3) to (4, 5, 6) (pF MAX)	<b>DCR (1-3)</b> (Ω MAX)	<b>dcr (4-6)</b> (Ω Max)	<b>МАХ (1-3)</b> ' (V-µsec Max)	<b>Turns Ratio</b> (1:3) (6:4)	<b>isolated Voltage</b> (Vrms)		
PH9384.011NL	538	0.8	20	0.30	0.40	24	1CT : 1CT			
PH9384.012NL	538	0.6	30	0.33	0.65	24	1CT : 2CT			
PH9384.021NL	538	1.6	15	0.30	0.25	24	2CT : 1CT			
PH9384.034NL	680	0.6	30	0.35	0.52	27	3CT : 4CT	4000		
PH9384.035NL	680	0.7	30	0.35	0.65	27	3CT : 5CT	4000		
PH9384.038NL	538	0.7	30	0.40	0.90	27	3CT : 8CT			
PH9384.043NL	538	0.8	20	0.30	0.30	24	4CT : 3CT			
PH9384.083NL	538	2.0	15	0.30	0.22	24	8CT : 3CT			
PH9384.089NL	538	0.6	30	0.30	0.42	24	8CT :9CT			

## Notes:

 The maximum volt-usec rating limits the peak flux density to 3600 gauss when used in bi-polar drive application with 200KHz. For unipolar drive applications or a bi-polar drive with 350kHz, a maximum volt-usec could be 60% of the listed value. For Push-Pull topology, where the voltage is applied across half the primary winding turns, the maximum volts-use needs to be derated by 50%. 2. Optional Tape & Reel packing can be ordered by adding a "**T**" suffix to the part number (i.e. PH9384.012NL becomes PH9384.012NL**T**). Pulse complies to industry standard tape and reel specification EIA481.

3. The "NL" suffix indicates an RoHS-compliant part number.



1

power.pulseelectronics.com

P775.H (03/18)


Toroid Platform SMD



## Application

PH9384NL is a series of high isolation power supply transformer drivers. Intended to operate in a fixed duty cycle Push Pull topology, it is a part of a low cost solution for delivering lower power (up to 3W) from a low voltage source. A typical implementation would be an isolated RS-485/RS-232 power supply driver circuit, the design is compatible with the MAXIM<sup>™</sup> MAX253 IC.

A schematic diagram for the Push Pull converter topology is given below.



For a fixed 50% duty cycle mode of operation, the output voltage is simply determined by the input voltage and turns ratio. So, with the available turns ratios, a variety of output voltages can be selected. PH9384.034NL has been certified by UL to comply with UL60950-12 edition with reinforced insulation for a working voltage up to 300Vac. 7mm creepage and 3000Vrms isolation voltage is guaranteed to meet this requirement. The actual isolation and creepage capability of the design

## exceeds these UL ratings

The remainder of the PH9384.xxxNL series was not included in the UL certification but are fully complaint with the requirements for reinforced insulation.

MAXIM is a registered trademark of Maxim Integrated Products.

For More Informatic Pulse Worldwide Headquarters 15255 Innovation Drive Ste 100 San Diego, CA 92128 U.S.A.	On Pulse Europe Pulse Electronics GmbH Am Rottland 12 58540 Meinerzhagen Germany	Pulse China Headquarters Pulse Electronics (ShenZhen) CO., LTD D708, Shenzhen Academy of Aerospace Technology, The 10th Keji South Road, Nanshan District, Shenzhen, P.R. China 518057	<b>Pulse North China</b> Room 2704/2705 Super Ocean Finance Ctr. 2067 Yan An Road West Shanghai 200336 China	<b>Pulse South Asia</b> 3 Fraser Street 0428 DUO Tower Singapore 189352	<b>Pulse North Asia</b> 1F., No.111 Xiyuan Rd Zhongli City Taoyuan City 32057 Taiwan (R.O.C)
Tel: 858 674 8100	Tel: 49 2354 777 100	Tel: 86 755 33966678	Tel: 86 21 62787060	Tel: 65 6287 8998	Tel: 886 3 4356768
Fax: 858 674 8262	Fax: 49 2354 777 168	Fax: 86 755 33966700	Fax: 86 2162786973	Fax: 65 6280 0080	Fax: 886 3 4356820

Performance warranty of products offered on this data sheet is limited to the parameters specified. Data is subject to change without notice. Other brand and product names mentioned herein may be trademarks or registered trademarks of their respective owners. © Copyright, 2018. Pulse Electronics, Inc. All rights reserved.

2