

PRODUCT-DETAILS

CT-MKC.31

CT-MKC.31 Time relay, Multifunctional solid-state, 12-240VAC/DC



General Information

Extended Product Type	CT-MKC.31
Product ID	1SVR508010R1300
EAN	4013614555626
Catalog Description	CT-MKC.31 Time relay, Multifunctional solid-state, 12-240VAC/DC
Long Description	CT-MKC.31 Time relay, Multifunctional solid-state, 12-240VAC/DC

Ordering

EAN	4013614555626
Minimum Order Quantity	1 piece
Customs Tariff Number	85364900

Container Information

Package Level 1 Units	1 piece
Package Level 1 Width	89 mm
Package Level 1 Depth / Length	20 mm
Package Level 1 Height	65 mm
Package Level 1 Gross Weight	0.065 kg
Package Level 1 EAN	4013614555626

Dimensions

Product Net Width	17.5 mm
Product Net Height	70 mm
Product Net Depth / Length	63 mm
Product Net Weight	0.053 kg

Technical

Timer Relay Type	Multifunction
Time Range	0.05 s ... 100 h
Rated Control Supply Voltage (U _s)	12 ... 240 V AC/DC
Rated Frequency (f)	50 Hz 60 Hz DC
Output	solid-state output
Terminal Type	Screw Terminals
Rated Operational Current AC-12 (I _e)	(230 V) 1 A
Rated Operational Current AC-15 (I _e)	(230 V) 0.25 A
Rated Operational Current DC-12 (I _e)	(24 V) 1 A
Rated Operational Current DC-13 (I _e)	(24 V) 1 A
Rated Insulation Voltage (U _i)	Input Circuit / Output Circuit 300 V
Degree of Protection	Housing IP50 Terminals IP20
Overvoltage Category	III
Pollution Degree	3
Connecting Capacity	Flexible 1x 0.5 ... 2.5 mm ² Flexible 2x 0.5 ... 1.5 mm ² Rigid 1x 0.5 ... 4 mm ² Rigid 2x 0.5 ... 1.5 mm ²
Tightening Torque	0.5 ... 0.8 N·m
Wire Stripping Length	7 mm
Mounting Position	Any
Mounting on DIN Rail	TH35-15 (35 x 15 mm Mounting Rail) acc. to IEC 60715 TH35-7.5 (35 x 7.5 mm Mounting Rail) acc. to IEC 60715
Standards	CAN/CSA C22.2 No.14 EN 50581 IEC/EN 61812-1 UL 60947-5-1

Environmental

Ambient Air Temperature	Operation -20 ... +60 °C Storage -40 ... +85 °C
RoHS Status	Following EU Directive 2011/65/EU

Technical UL/CSA

Connecting Capacity UL/CSA	Flexible 1x 18-14 AWG Flexible 2x 18-16 AWG Rigid 1x 20-12 AWG Rigid 2x 20-16 AWG
Tightening Torque UL/CSA	4.43 ... 7.08 in·lb

Certificates and Declarations (Document Number)

CCC Certificate	CCC_2019010303150608
cULus Certificate	cULus_20031209-E140448
Data Sheet, Technical Information	2CDC111163C0201
Declaration of Conformity - CE	1SVD981068
Instructions and Manuals	1SVC500020M0001
RoHS Information	1SVD981068

Classifications

Object Classification Code	K
ETIM 5	EC001439 - Timer relay
ETIM 6	EC001439 - Timer relay
ETIM 7	EC001439 - Timer relay
eClass	7.0 27371790
UNSPSC	39121519

Categories

Low Voltage Products and Systems → Control Products → Electronic Relays and Controls → Time Relays

