

Coaxial Cable Connector 11_N-50-7-6/133_N

Description

Straight cable plug

Interface standards

IEC 61169-16_MIL-STD-348A/304_CECC 22210



Technical Data

Electrical Data

Impedance	50 Ω
Interface frequency max.	11 GHz

Mechanical Data

Centre contact	soldered
Outer 2contact	clamped
Weight	0.0505 kg

Environmental Data

Operating temperature	-65 °C to 165 °C
2011/65/EU (RoHS)	compliant

Material Data

Piece Parts	Material	Surface Plating
Centre contact	Brass	Gold Plating (Nickel underplated)
Outer contact	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	
Coupling nut	Brass	SUCOPLATE (R) Plating
Gasket	VMQ (Silicone rubber)	

Related Documents

Catalogue drawing	DOU-00006550
Assembly instruction	DOC-0000179854

Ordering Information

Single package	11_N-50-7-6/133_NE
----------------	--------------------

Additional Information

Suitable cables	RG_214_/U, GX_07272, RG_213_/U, GX_07272_D-04
-----------------	-----------------------------------------------