

Electrical:

- Impedance: Non-constant
- Frequency Range: 0~300 MHz
- Voltage Rating: ≥ 750 V rms.(depending on cable)
- Insulator Resistance: ≥ 5 G Ω
- Dielectric Withstanding Voltage: 2000 V rms
- Contact Resistance: Center Contact ≤ 5 m Ω
Outer Contact ≤ 5 m Ω



Mechanical:

- Mating: 5/8-24 UNEF Screw-on Coupling

Environmental:

- Temperature Range: -25°C to 70°C
- Corrosion (Salt Spray): MIL-STD-202, Method 101, Cond. C
- Thermal Shock: MIL-STD-202, Method 107, Cond. B
- Mechanical: MIL-STD-202, Method 213, Cond. G
- Vibration: MIL-STD-202, Method 204, Cond. B

Finish [Unit of Plating Thickness Is in Micro Inch(μ)]:

1. Nickel Plating Thickness: 50 μ " min. (Under Plating)
2. Gold Plating Thickness: 2 μ " max. (Over Finish 1)

Item	Description	Material	Finish
1	Body	Diecast	Finish 1
2	Insulator	PTFE	None
3	Inner Contact	Brass	Finish 1/2

