

**EVO-STIK KITCHEN, SHOWER AND BATHROOM
SEALANT WHITE**
Supersedes Date: 07-Dec-2016

Revision Date 04-Jun-2018

Revision Number 1.01

Section 1: IDENTIFICATION OF THE SUBSTANCE/MIXTURE AND OF THE COMPANY/UNDERTAKING

1.1. Product Identifier

Product Name EVO-STIK KITCHEN, SHOWER AND BATHROOM SEALANT WHITE
Pure substance/mixture Mixture

1.2. Relevant identified uses of the substance or mixture and uses advised against

Recommended use Sealant.
Uses advised against None known

1.3. Details of the supplier of the safety data sheet

Company Name

Bostik Limited
Common Rd
ST16 3EH
Stafford UK
Tel: +44 (1785) 27 26 25
Fax: +44 (1785) 25 72 36

E-mail address SDS.box-EU@bostik.com

1.4. Emergency telephone number

United Kingdom	+44 (1785) 272650
Ireland	+353 (1) 8624900 (Monday- Friday 9am-5pm)

Section 2: HAZARDS IDENTIFICATION

2.1. Classification of the substance or mixture

Classification according to Regulation (EC) No. 1272/2008 [CLP]

Not classified

2.2. Label Elements

Labelling according to Regulation (EC) No. 1272/2008 [CLP]

Not classified

Signal Word

No signal word

Special provisions concerning the labelling of certain mixtures

EUH208 - Contains 1,2-Benzisothiazolin-3-one. May produce an allergic reaction

Precautionary Statements - EU (§28, 1272/2008)

P101 - If medical advice is needed, have product container or label at hand

P102 - Keep out of reach of children

P280 - Wear protective gloves and eye/face protection

P305 + P351 + P338 - IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing

Safety Data Sheet

EVO-STIK KITCHEN, SHOWER AND BATHROOM
SEALANT WHITE
Supersedes Date: 07-Dec-2016

Revision Date 04-Jun-2018

Revision Number 1.01

P332 + P313 - If skin irritation occurs: Get medical advice/attention

2.3. Other Hazards

General Hazards

No information available.

PBT and vPvB assessment

The components in this formulation do not meet the criteria for classification as PBT or vPvB

Section 3: COMPOSITION/INFORMATION ON INGREDIENTS

3.1 Substances

Not applicable

3.2 Mixtures

Chemical Name	EC No	CAS No	Weight-%	Classification according to Regulation (EC) No. 1272/2008 [CLP]	Specific concentration limit (SCL)	REACH Registration Number
Propanol, oxybis-, dibenzoate	248-258-5	27138-31-4	1- <2.5	Aquatic Chronic 3 (H412)		01-2119529241-49-XXXX
Ammonium hydroxide	215-647-6	1336-21-6	0.1 - <1	Skin Corr. 1B (H314) Aquatic Acute 1 (H400) STOT SE 3 (H335)	STOT SE 3 :: C>=5%	01-2119982985-14-XXXX
1,2-Benzisothiazolin-3-one	220-120-9	2634-33-5	0.0015 - <0.01	Acute Tox. 4 (H302) Skin Irrit. 2 (H315) Eye Dam. 1 (H318) Skin Sens. 1 (H317) Aquatic Acute 1 (H400) Acute Tox. 2 (H330) Aquatic Chronic 2 (H411)	Skin Sens. 1 :: C>=0.05%	No data available
Zinc pyrithione	236-671-3	13463-41-7	<0.0015	Eye Dam. 1 (H318) Acute Tox. 3 (H301) Acute Tox. 3 (H331) Aquatic Acute 1 (H400) Aquatic Chronic 1 (H410)		01-2119511196-46-XXXX

Full text of H- and EUH-phrases: see section 16

Note: ^ indicates not classified, however, the substance is listed in section 3 as it has an OEL.

This product does not contain candidate substances of very high concern at a concentration $\geq 0.1\%$ (Regulation (EC) No. 1907/2006 (REACH), Article 59)

Section 4: FIRST AID MEASURES

Safety Data Sheet

EVO-STIK KITCHEN, SHOWER AND BATHROOM
SEALANT WHITE
Supercedes Date: 07-Dec-2016

Revision Date 04-Jun-2018

Revision Number 1.01

4.1. Description of first aid measures

General Advice	If medical advice is needed, have product container or label at hand. In the case of skin irritation or allergic reactions see a doctor.
Inhalation	IF INHALED: Remove victim to fresh air and keep at rest in a position comfortable for breathing.
Skin Contact	Wash off immediately with plenty of water for at least 15 minutes. In the case of skin irritation or allergic reactions see a doctor.
Eye contact	Rinse immediately with plenty of water, also under the eyelids, for at least 15 minutes. Do not rub affected area. If eye irritation persists: Get medical advice/attention.
Ingestion	If symptoms persist, call a doctor. Do not induce vomiting without medical advice. Never give anything by mouth to an unconscious person.
Self-Protection of the First Aider	Use personal protective equipment as required.

4.2. Most important symptoms and effects, both acute and delayed

Symptoms None known.

4.3. Indication of any immediate medical attention and special treatment needed

Note to doctors Treat symptomatically.

Section 5: FIREFIGHTING MEASURES

5.1. Extinguishing media

Suitable Extinguishing Media

Water spray (fog). Carbon dioxide (CO₂). Foam. Dry chemical. Use extinguishing measures that are appropriate to local circumstances and the surrounding environment.

Unsuitable Extinguishing Media

None known

5.2. Special hazards arising from the substance or mixture

Thermal decomposition can lead to release of irritating and toxic gases and vapours.

Hazardous Combustion Products Carbon monoxide. Carbon dioxide (CO₂). Hydrocarbons.

5.3. Advice for firefighters

Wear self-contained breathing apparatus and protective suit.

Section 6: ACCIDENTAL RELEASE MEASURES

6.1. Personal precautions, protective equipment and emergency procedures

Personal Precautions

Evacuate personnel to safe areas. Use personal protection recommended in Section 8.

For emergency responders

Use personal protection recommended in Section 8.

6.2. Environmental precautions

Keep people away from and upwind of spill/leak.

Safety Data Sheet

EVO-STIK KITCHEN, SHOWER AND BATHROOM
SEALANT WHITE
Supercedes Date: 07-Dec-2016

Revision Date 04-Jun-2018

Revision Number 1.01

6.3. Methods and material for containment and cleaning up

Methods for Containment Stop leak if you can do it without risk.

Methods for cleaning up Cover liquid spill with sand, earth or other non-combustible absorbent material. Cover powder spill with plastic sheet or tarp to minimise spreading. Pick up and transfer to properly labelled containers.

6.4. Reference to other sections

Reference to other sections Section 8: EXPOSURE CONTROLS/PERSONAL PROTECTION
Section 13: DISPOSAL CONSIDERATIONS

Section 7: HANDLING AND STORAGE

7.1. Precautions for safe handling

Advice on safe handling

Avoid contact with skin, eyes or clothing. Wash hands thoroughly after handling. Handle in accordance with good industrial hygiene and safety practice. Do not re-use container.

General Hygiene Considerations

Handle in accordance with good industrial hygiene and safety practice.

7.2. Conditions for safe storage, including any incompatibilities

Storage Conditions

Keep from freezing. Keep containers tightly closed in a cool, well-ventilated place.

7.3. Specific end use(s)

Other Information

Recommendation(s). Observe technical data sheet.

Section 8: EXPOSURE CONTROLS/PERSONAL PROTECTION

8.1. Control parameters

Derived No Effect Level (DNEL) No information available

Predicted No Effect Concentration (PNEC) No information available.

8.2. Exposure controls

Engineering Controls Use with local exhaust ventilation. Ensure adequate ventilation, especially in confined areas. Use explosion-proof ventilating equipment.

Personal Protective Equipment

Eye/Face Protection Wear safety glasses with side shields (or goggles). Avoid contact with eyes.
Skin and Body Protection Wear protective gloves and protective clothing. Avoid contact with skin, eyes or clothing.
Respiratory Protection During spraying wear suitable respiratory equipment.

Environmental Exposure Controls Do not allow into any sewer, on the ground or into any body of water.

Section 9: PHYSICAL AND CHEMICAL PROPERTIES

9.1. Information on basic physical and chemical properties

Physical State Paste / Gel Liquid
Appearance Paste

Safety Data Sheet

EVO-STIK KITCHEN, SHOWER AND BATHROOM
SEALANT WHITE
Supercedes Date: 07-Dec-2016

Revision Date 04-Jun-2018

Revision Number 1.01

Colour White
Odour Characteristic
Odour Threshold No information available

<u>Property</u>	<u>Values</u>	<u>Remarks • Method</u>
pH	No information available	
Melting point / freezing point	No information available	
Boiling point / boiling range	No information available	
Flash Point	No information available	
Evaporation Rate	No information available	
Flammability (solid, gas)	No information available	Not applicable for liquids
Flammability Limit in Air		
Upper flammability limit:	No information available	
Lower flammability limit	No information available	
Vapour Pressure	No information available	
Vapour Density	No information available	
Relative Density	No information available	
Water Solubility	No information available	
Solubility in Other Solvents	No information available	
Partition Coefficient	No information available	
Autoignition Temperature	No information available	
Decomposition Temperature	No information available	
Explosive Properties	No information available	
Explosive Limits	No information available	
Upper	No information available	
Lower	No information available	
Oxidising Properties	No information available	
Kinematic Viscosity	No information available	
Dynamic Viscosity	No information available	

9.2. Other information

Softening Point No information available
Molecular Weight No information available
Solvent content (%) No information available
Solid content (%) approx 77
Density 1.7
Bulk Density No data available
VOC content (%) 3.4 %

Section 10: STABILITY AND REACTIVITY

10.1. Reactivity

None under normal use conditions.

10.2. Chemical stability

Stable under normal conditions.

Explosion Data

Sensitivity to Mechanical Impact None.
Sensitivity to Static Discharge None.

10.3. Possibility of hazardous reactions

Hazardous Polymerisation

None known.

Possibility of Hazardous Reactions

None under normal processing.

Safety Data Sheet

EVO-STIK KITCHEN, SHOWER AND BATHROOM
SEALANT WHITE
Supercedes Date: 07-Dec-2016

Revision Date 04-Jun-2018

Revision Number 1.01

10.4. Conditions to avoid

Extremes of temperature and direct sunlight. Keep from freezing.

10.5. Incompatible materials

No information available.

10.6. Hazardous decomposition products

Carbon monoxide. Carbon dioxide (CO₂). Hydrocarbons.

Section 11: TOXICOLOGICAL INFORMATION

11.1. Information on toxicological effects

Information on likely routes of exposure

Product Information

No information or data specific to the product on this toxicological (health) effect is available.

Inhalation	Based on available data, the classification criteria are not met.
Eye contact	Based on available data, the classification criteria are not met.
Skin Contact	Based on available data, the classification criteria are not met.
Ingestion	Based on available data, the classification criteria are not met.
Sensitisation	No data available.

Delayed and immediate effects as well as chronic effects from short and long-term exposure

Skin Corrosion/Irritation	Not applicable.
Serious eye damage/eye irritation	Not applicable.
Sensitisation	Not applicable.
Germ Cell Mutagenicity	Not applicable.
Carcinogenicity	Not applicable.
Reproductive Toxicity	No information available.
STOT - Single Exposure	No information available.
STOT - Repeated Exposure	Causes damage to organs through prolonged or repeated exposure.
Aspiration hazard	No information available.

Numerical measures of toxicity

Acute Toxicity

The following values are calculated based on chapter 3.1 of the GHS document mg/kg

Component Information

Toxicity Data Data obtained on the component(s) include

Chemical Name	Oral LD50	Dermal LD50	Inhalation LC50
Propanol, oxybis-, dibenzoate 27138-31-4	= 3914 mg/kg (Rat)	> 2000 mg/kg (rat)	-

Safety Data Sheet

EVO-STIK KITCHEN, SHOWER AND BATHROOM
SEALANT WHITE
Supercedes Date: 07-Dec-2016

Revision Date 04-Jun-2018

Revision Number 1.01

Ammonium hydroxide 1336-21-6	>2000 mg/kg (Rat)	-	-
---------------------------------	---------------------	---	---

Section 12: ECOLOGICAL INFORMATION

12.1. Toxicity

Ecotoxicity No information available

Component Information

Data obtained on the component(s) include

Chemical Name	Algae/aquatic plants	Fish	Crustacea	M-Factor
Propanol, oxybis-, dibenzoate 27138-31-4	-	3.7 mg/l (fathead minnow)	EL50 (48h) = 19.3 mg/l (Daphnia magna)	
Ammonium hydroxide 1336-21-6	-	LC50 96 h = 8.2 mg/L (Pimephales promelas)	LC50 (48h) = 101 mg/L (Daphnia magna) ASTM E729-80	
1,2-Benzisothiazolin-3-one 2634-33-5	EC50 3Hr 13mg/l (activated sludge) (OECD 209)	-	-	1
Zinc pyrithione 13463-41-7	-	-	EC50 (48h) =0.038 mg/L Crustaceans (Ilyocypris dentifera)	100

12.2. Persistence and degradability

No information available.

12.3. Bioaccumulative potential

No information available.

Partition coefficient No information available

12.4. Mobility in soil

Mobility in soil No information available.

12.5. Results of PBT and vPvB assessment

The components in this formulation do not meet the criteria for classification as PBT or vPvB.

12.6. Other adverse effects

No information available

Endocrine Disruptor Information

This product does not contain any known or suspected endocrine disruptors.

Section 13: DISPOSAL CONSIDERATIONS

13.1. Waste treatment methods

Waste from Residues/Unused Products Disposal should be in accordance with applicable regional, national and local laws and regulations.

Contaminated Packaging Improper disposal or reuse of this container may be dangerous and illegal.

Safety Data Sheet

EVO-STIK KITCHEN, SHOWER AND BATHROOM
SEALANT WHITE
Supercedes Date: 07-Dec-2016

Revision Date 04-Jun-2018

Revision Number 1.01

Other Information

Waste codes should be assigned by the user based on the application for which the product was used.

Section 14: TRANSPORT INFORMATION

ADR

14.1 UN/ID no	Not regulated
14.2 Proper Shipping Name	Not regulated
14.3 Transport hazard class(es)	Not regulated
14.4 Packing Group	Not regulated
14.5 Environmental Hazard	Not applicable
14.6 Special Provisions	None

IMDG

14.1 UN Number	Not regulated
14.2 Proper Shipping Name	Not regulated
14.3 Transport hazard class(es)	Not regulated
14.4 Packing Group	Not regulated
14.5 Marine Pollutant	Np
14.6 Special Provisions	None
14.7 Transport in bulk according to Annex II of MARPOL 73/78 and the IBC Code	No information available

RID

14.1 UN Number	Not regulated
14.2 Proper Shipping Name	Not regulated
14.3 Transport hazard class(es)	Not regulated
14.4 Packing Group	Not regulated
14.5 Environmental Hazard	Not applicable
14.6 Special Provisions	None

ICAO (air)

14.1 UN/ID no	Not regulated
14.2 Proper Shipping Name	Not regulated
14.3 Hazard Class	Not regulated
14.4 Packing Group	Not regulated
14.5 Environmental Hazard	Not applicable
14.6 Special Provisions	None

IATA

14.1 UN/ID no	Not regulated
14.2 Proper Shipping Name	Not regulated
14.3 Transport hazard class(es)	Not regulated
14.4 Packing Group	Not regulated
14.5 Environmental Hazard	Not applicable
14.6 Special Provisions	None

Section 15: REGULATORY INFORMATION

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

European Union

Take note of Directive 98/24/EC on the protection of the health and safety of workers from the risks related to chemical agents at work

Check whether measures in accordance with Directive 94/33/EC for the protection of young people at work must be taken.

Take note of Directive 92/85/EC on the protection of pregnant and breastfeeding women at work

Safety Data Sheet

EVO-STIK KITCHEN, SHOWER AND BATHROOM
SEALANT WHITE
Supercedes Date: 07-Dec-2016

Revision Date 04-Jun-2018

Revision Number 1.01

Registration, Evaluation, Authorization, and Restriction of Chemicals (REACH) Regulation (EC 1907/2006)

EU-REACH (1907/2006) - Candidate List of Substances of Very High Concern (SVHC) for Authorization in accordance with Article 59

This product does not contain candidate substances of very high concern at a concentration $\geq 0.1\%$ (Regulation (EC) No. 1907/2006 (REACH), Article 59)

EU-REACH (1907/2006) - Annex XVII - Substances subject to Restriction

This product does not contain substances subject to restriction (Regulation (EC) No. 1907/2006 (REACH), Annex XVII).

EU-REACH (1907/2006) - Annex XIV - List of substances subject to Authorization

This product does not contain substances subject to authorisation (Regulation (EC) No. 1907/2006 (REACH), Annex XIV)

Ozone-depleting substances (ODS) regulation (EC) 1005/2009

Not applicable

Persistent Organic Pollutants

Not applicable

15.2. Chemical safety assessment

None

Section 16: OTHER INFORMATION

Key or legend to abbreviations and acronyms used in the safety data sheet

Full text of H-Statements referred to under section 3

H314 - Causes severe skin burns and eye damage
H400 - Very toxic to aquatic life
H335 - May cause respiratory irritation
H318 - Causes serious eye damage
H301 - Toxic if swallowed
H331 - Toxic if inhaled
H410 - Very toxic to aquatic life with long lasting effects
H302 - Harmful if swallowed
H315 - Causes skin irritation
H317 - May cause an allergic skin reaction
H330 - Fatal if inhaled
H411 - Toxic to aquatic life with long lasting effects
H412 - Harmful to aquatic life with long lasting effects

Legend

SVHC: Substances of Very High Concern for Authorisation:

Legend Section 8: Exposure controls and personal protection

TWA	TWA (time-weighted average)	STEL	STEL (Short Term Exposure Limit)
Ceiling	Maximum limit value	*	Skin designation
PBT	Persistent, Bioaccumulative, and Toxic (PBT) Chemicals		
STOT (RE):	Specific target organ toxicity - Repeated exposure		
STOT (SE):	Specific target organ toxicity - Single exposure		
EWC:	European Waste Catalogue		

Safety Data Sheet

EVO-STIK KITCHEN, SHOWER AND BATHROOM
SEALANT WHITE
Supercedes Date: 07-Dec-2016

Revision Date 04-Jun-2018

Revision Number 1.01

Key literature references and sources for data

Classification and labeling data calculated from data received from raw material suppliers

Prepared By Product Safety & Regulatory Affairs

Revision Date 04-Jun-2018

Indication of changes

Revision Note Not applicable.

Training Advice No information available

Further information No information available

This safety data sheet complies with the requirements of: Regulation (EC) No. 1907/2006

Disclaimer

The information provided in this Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information given is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal and release and is not to be considered a warranty or quality specification. The information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process, unless specified in the text.

End of Safety Data Sheet