Regulation EC No 1907/2006 Art.31

CT-90 Creationdate: 07.02.22 Version: 2.2 Productname:

Ref.Nr.: UDS000761 3 20220207 (EN) Replaces: UDS000761 20210929

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

CT-90

Bulk

1.2. Relevant identified uses of the substance or mixture and uses advised against

Lubricants

1.3. Details of the supplier of the safety data sheet

CRC Industries UK Ltd. Wylds Road **Castlefield Industrial Estate TA6 4DD Bridgwater Somerset United Kingdom**

Tel.: +44 1278 727200 Fax.: +44 1278 425644 E-mail: hse.uk@crcind.com

1.4. Emergency telephone number

(+44)(0)1278 72 7200 (office hours)

SECTION 2: Hazards identification

2.1. Classification of the substance or mixture

Classification according to Regulation (EC) No 1272/2008

Physical: Not classified

Classification is based on test data.

Health: Effects on or via Lactation

May cause harm to breast-fed children.

Classification based on calculation method.

Environment: Hazardous to the aquatic environment, chronic category 1

Very toxic to aquatic life with long lasting effects.

Classification based on calculation method.

Other hazards: Repeated exposure may cause skin dryness or cracking.

2.2. Label elements



1/8

Regulation EC No 1907/2006 Art.31

CT-90 Creationdate: 07.02.22 Version: 2.2 Productname:

Ref.Nr.: UDS000761 3 20220207 (EN) Replaces: UDS000761 20210929

Labelling according to Regulation (EC) No 1272/2008

Hazard pictogram(s):

Signal word: Warning

Hazard statement(s): H362: May cause harm to breast-fed children.

H410: Very toxic to aquatic life with long lasting effects.

P101: If medical advice is needed, have product container or label at hand. Precautionary statement(s):

P102: Keep out of reach of children.

P263: Avoid contact during pregnancy/while nursing.

P273 : Avoid release to the environment.

P391 : Collect spillage.

P501-2: Dispose of contents/container to an authorised waste collection point.

Supplemental Hazard

Repeated exposure may cause skin dryness or cracking. information:

2.3. Other hazards

Alkanes, C14-17, chloro

SECTION 3: Composition/information on ingredients

3.1. Substances

Not applicable.

3.2. Mixtures

Hazardous ingredient	Registration number	CAS-nr.	EC-nr	w/w %	Hazard Class and Category	Hazard statement	Notes	
Alkanes, C14-17, chloro	01-2119519269-33	85535-85- 9	287-477- 0	25-50	Lact., Aquatic Acute 1, Aquatic Chronic 1	H362,H400,H410	I,C,D	
Highly refined base oil	-	-	-	25-50	-	-		
Explanation notes								
C : PBT-substance								
D : vPvB-substance								
I : SVHC (substance of very high concern)in accordance with art.57 of REACH Regulation No 1907/2006								

^{(*} Explanation phrases : see chapter 16)

SECTION 4: First aid measures

4.1. Description of first aid measures

Contact with eyes: If substance has got into eyes, immediately wash out with plenty of water for

several minutes

Seek medical attention if irritation persists



2/8

Regulation EC No 1907/2006 Art.31

 Productname :
 CT-90
 Creationdate :
 07.02.22 Version : 2.2

 Ref.Nr.:
 UDS000761_3_20220207 (EN)
 Replaces:
 UDS000761_20210929

Contact with skin: Wash with water and soap.

Seek medical attention if irritation persists

Inhalation: Fresh air, keep warm and at rest.

Seek medical attention if ill effects occur

Ingestion: If swallowed do not induce vomiting

Seek medical advice

4.2. Most important symptoms and effects, both acute and delayed

Inhalation: Excessive inhalation of solvent vapours may give rise to nausea, headaches

and dizziness

Ingestion: May cause gastrointestinal disturbances

Symptoms: sore throat, abdominal pain, nausea, vomiting

Skin contact : Mildly irritating to skin

Symptoms: redness and pain

Eye contact : Mildly irritating to eyes

Symptoms: redness and pain

4.3. Indication of any immediate medical attention and special treatment needed

General Advice: If you feel unwell, seek medical advice (show the label where possible

If symptoms persist always call a doctor

SECTION 5: Firefighting measures

5.1. Extinguishing media

foam, carbon dioxide or dry agent

5.2. Special hazards arising from the substance or mixture

Forms hazardous decomposition products CO,CO2

5.3. Advice for firefighters

Keep container(s) exposed to fire cool, by spraying with water In case of fire, do not breathe fumes

SECTION 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

Shut off all ignition sources Ensure adequate ventilation

Wear suitable protective clothing including eye/face protection.

6.2. Environmental precautions



3/8

Regulation EC No 1907/2006 Art.31

CT-90 Productname:

Creationdate: 07.02.22 Version: 2.2 Ref.Nr.: UDS000761 3 20220207 (EN) Replaces: UDS000761 20210929

Do not allow to enter public sewers and watercourses

If polluted water reaches drainage systems or water courses, immediately inform appropriate authorities

6.3. Methods and material for containment and cleaning up

Absorb spillage in suitable inert material

6.4. Reference to other sections

For further information see section 8

SECTION 7: Handling and storage

7.1. Precautions for safe handling

Use only in well ventilated areas

Avoid contact with skin and eyes.

Wash thoroughly after use

Wear protective gloves/protective clothing/eye protection/face protection.

7.2. Conditions for safe storage, including any incompatibilities

Keep in a cool, dry, well ventilated place

Keep out of reach of children.

7.3. Specific end use(s)

Lubricants

SECTION 8: Exposure controls/personal protection

8.1. Control parameters

Exposure limits:

Hazardous ingredient	CAS-nr.	method	
National established exposure limits, United Kingdom			
Highly refined base oil	-	TWA	5 mg/m3
		STEL	10 mg/m3

8.2. Exposure controls

Control procedures: Ensure adequate ventilation

Take precautions to avoid contact with skin and eyes when handling the Personal protection:

product.

Ensure adequate ventilation



4/8

Regulation EC No 1907/2006 Art.31

CT-90 Creationdate: 07.02.22 Version: 2.2 Productname: Ref.Nr.: UDS000761 3 20220207 (EN) Replaces: UDS000761 20210929

inhalation: In case of insufficient ventilation, wear suitable respiratory equipment. recommended respiratory protection: Air purifying respirator equiped with organic gas/vapor cartridge (type A) hands and skin: When handling the product wear chemical-resistant gloves (standard EN 374). The breakthrough time of the glove should be longer than the total duration of product use. If work lasts longer than the breakthrough time, gloves should be changed part-way through. Recommended gloves:

Wear safety eyewear according to EN 166. eyes:

SECTION 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

Appearance : physical state : Liquid. colour: Yellow. odour: Oil.

Not applicable. pH: Boiling point/range: Not available. 221 °C (Open Cup) Flash point: Evaporation rate: Not available. Explosion limits: upper limit: Not available. lower limit: Not available. Vapour pressure: Not available. Relative density: 1.05 g/cm3 (@ 15°C).

Solubility in water: Insoluble in water Auto-ignition: Not available. Viscosity: >144 cSt @ 40°C

9.2. Other information

SECTION 10: Stability and reactivity

10.1. Reactivity

No hazardous reactions known if used for its intended purpose

10.2. Chemical stability

Stable

10.3. Possibility of hazardous reactions

No hazardous reactions known if used for its intended purpose

10.4. Conditions to avoid

Avoid overheating



Regulation EC No 1907/2006 Art.31

Productname: CT-90

Ref.Nr.: UDS000761_3_20220207 (EN)

Creationdate : Replaces:

07.02.22 Version : 2.2 UDS000761_20210929

10.5. Incompatible materials

Strong oxidising agent

10.6. Hazardous decomposition products

CO,CO2

SECTION 11: Toxicological information

11.1. Information on toxicological effects

acute toxicity:	based on available data the classification criteria are not met
skin corrosion/irritation:	based on available data the classification criteria are not met
serious eye damage/irritation:	based on available data the classification criteria are not met
respiratory or skin sensitisation:	based on available data the classification criteria are not met
germ cell mutagenicity:	based on available data the classification criteria are not met
carcinogenicity:	based on available data the classification criteria are not met
toxicity for reproduction:	based on available data the classification criteria are not met
STOT-single exposure:	based on available data the classification criteria are not met
STOT repeated exposure:	based on available data the classification criteria are not met
aspiration hazard:	based on available data the classification criteria are not met

Information on likely routes of exposure:

Inhalation: Inhalation of solvent vapours may give rise to nausea, headaches and

dizziness

Ingestion: May cause gastrointestinal disturbances

Skin contact : May cause irritation. **Eye contact :** May cause irritation.

Toxicological data:

No information available

SECTION 12: Ecological information

12.1. Toxicity

Hazardous to the aquatic environment, chronic category 1 Very toxic to aquatic life with long lasting effects.

Ecotoxicological data:

No information available



6/8

Ref.Nr.:

Regulation EC No 1907/2006 Art.31

Productname: CT-90

UDS000761 3 20220207 (EN)

Creationdate : Replaces:

07.02.22 Version : 2.2 UDS000761 20210929

12.2. Persistence and degradability

No information available

12.3. Bioaccumulative potential

No information available

12.4. Mobility in soil

Insoluble in water

12.5. Results of PBT and vPvB assessment

Alkanes, C14-17, chloro

12.6. Other adverse effects

No information available

SECTION 13: Disposal considerations

13.1. Waste treatment methods

Do not discharge into drains or the environment, dispose to an authorised waste collection point.

SECTION 14: Transport information

14.1. UN number

UN-number: 3082

14.2. UN proper shipping name

Proper shipping name: ENVIRONMENTALLY HAZARDOUS SUBSTANCE, LIQUID, N.O.S. (Alkanes,

C14-17,chloro-)

14.3. Transport hazard class(es)

Class: 9
ADR/RID - Classification code: M6

14.4. Packing group

Packing group: III



7/8

Regulation EC No 1907/2006 Art.31

Creationdate: 07.02.22 Version: 2.2 Productname: CT-90

Ref.Nr.: UDS000761 3 20220207 (EN) Replaces: UDS000761 20210929

14.5. Environmental hazards

ADR/RID - Environmentally

Yes

hazardous:

Marine pollutant

IMDG - Marine pollutant: IATA/ICAO - Environmentally

Yes

hazardous:

14.6. Special precautions for user

ADR/RID - Tunnelcode: (E)

IMDG - Ems: F-A, S-F

14.7. Transport in bulk according to Annex II of MARPOL and the IBC Code

Not applicable.

SECTION 15: Regulatory information

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

The Safety Data Sheet is compiled according to the current European requirements.

Regulation (EC) No 1907/2006 (REACH)

Regulation (EC) No 1272/2008 (CLP)

15.2. Chemical safety assessment

No information available

SECTION 16: Other information

*Explanation hazard statements: -:-

H362: May cause harm to breast-fed children.

H400: Very toxic to aquatic life.

H410: Very toxic to aquatic life with long lasting effects.

TWA = time weight average acronyms and synonyms:

STEL = short time exposure limit VOC = volatile organic compounds PBT = persistant bioaccumulative toxic vPvB = very persitant very bioaccumulative

This product should be stored, handled and used in accordance with good industrial hygiene practices and in conformity with any legal regulation.

The information contained herewith is based on the present state of our knowledge and is intended to describe our products from the point of view of safety requirements. It does not guarantee any specific properties. Apart from any fair dealing for purposes of study, research and review of health, safety and environmental risks, no part of these documents may be reproduced by any process without written permission from CRC.

