


FT-30-A-A-M8

Fibre optics



Product characteristics
Diffuse reflection sensor

M8

Range 70 mm

Connection to fibre optic amplifiers type OIF

Range

Range

OIF: 70 mm

Environment

Ambient temperature [°C]

-40...290

Mechanical data

Design

straight

Length [mm]

600

Min. bending radius [mm]

30, for fixed installation

Fiber arrangement



Fibre optic

glass

Sensing head

aluminium

Sheathing

aluminium; adapter: polyamide

Weight [kg]

0.093

Accessories

Accessories (included)

2 hexagon nuts; M8; stainless steel; 2 tooth lock washers; 1 knurled nut; M30

Remarks

Pack quantity [piece]

1