

## Solid carbide end mill

3 cutting edges, uncoated

**ATORN®**



### Application

End mill for universal use when plunge milling, groove milling and keyway cutting as well as face milling and peripheral milling.

### Version

- solid carbide ultra-fine grain
- straight shank in accordance with DIN 6535 HB
- centre cutting
- radial relief
- with clearance
- uncoated

Application	Steel (N/mm <sup>2</sup> )			Stainless steel		Alu		Brass		Bronze		Plas-tics	Graphite G(C)FK	GG(G) GjMW	Titan-alloy	Nickel-alloy	Super-alloy	Hard mat.	
	<700	<1000	<1300	marten.	austen.	short	long	short	long	short	long							<55 HRC	<65 HRC
	105	80	65	60	55	225	270	145	160		115	115		90	50	45	40		

<b>Art. no.</b>	<b>16787 068</b>
<b>Cutting material</b>	VHM
<b>Surface</b>	Uncoated
<b>Type</b>	N
<b>Number of cutting edges</b>	3 PCS
<b>Twist angle</b>	30°
<b>Tool holding device</b>	HB parallel shank
<b>Overall length</b>	Normal
<b>Cutting edge diameter</b>	6.8 mm
<b>Cutting edge length</b>	16 mm
<b>Clearance length</b>	25 mm
<b>Length</b>	63 mm
<b>Edge protection chamfer length</b>	0.1 mm
<b>Clearance diameter</b>	6.6 mm
<b>Shaft diameter</b>	8 mm
<b>fz steel 1000</b>	0.03 mm
<b>Overall stainless steel suitability</b>	1
<b>fitness not iron total</b>	2
<b>fitness Titan/Nickel/Super total</b>	2

### EAN-Code

4050293090864