

SSDC clamping holder, positive neutral

For longitudinal turning with SC indexable insert

ATORN[®]

Application

For longitudinal turning with SC indexable insert, 45°

Version

- precision-manufactured steel carrier, bronzed, hardened, type S, attack angle 45°, tip angle 90°, clearance angle 7°

Advantage

- Robust geometry for longitudinal turning
- positive body geometry ensures low cutting forces



Art. no.	17849 153
ISO name	SSDC N 1616 H12
Shaft height	16 mm
Shank width	16 mm
Length	100 mm
Length of head	25 mm
Programming size	8 mm
Suitable for indexable inserts	SC.. 1204..
Tool design	Neutral

EAN-Code

4050293563269