

Drawer cabinet system 700 S with 5 SOFT-CLOSE drawers

Depth 700 mm, width 722 mm


Application:

Particularly suitable for careful storage of delicate, sensitive tools and parts in drawers.

Advantage:

- The damping system brakes the drawer while closing; it closes the drawer smoothly and soundlessly by means of the self-closing mechanism
- Impact load on tools and parts stored in the drawer is reduced to a minimum due to the smooth-closing drawers
- High quality - made in Germany

Art. no.	50300 712
Brand	HK
Manufacturer Part Number	50300712
Number of drawers	5 PCS
Height	800 mm
Width	722 mm
Depth	700 mm
Height x width x depth	800 x 722 x 700 mm
Drawer width (inner dimension) x drawer depth (inner dimension)	600 x 600 mm
Drawer with slots	Yes
Perforated drawer base	Yes
Load-carrying capacity per drawer	100 kg
Drawer surface	0.36 m ²
Pullout type	Full extension
With SOFT-CLOSE closing function	Yes
With single pull-out safety brake	Yes
Central locking	Yes
With cover panel	No
Material of cover panel	Wood, plastic-coated
Cabinet colour	Optional
Colour of front	Optional
Surface	Powder-coated
Functions	RFID possible
Model	S7 24/5
Overall surface	1.8 m ²
Lock type	DOM® locking system
Material	Sheet steel
Gross Weight	100.000 kg
Product Group	5BB



EAN

4053625049929