Belden

TECHNICAL DATA SHEET

concept

code version 1

date **2004-04-27**

4504FE NON-PAIRED page 1/2

APPLICATION

Intercom/PA Systems, Sound/Audio Systems.

CONSTRUCTION



1. Conductor

Diameter of conductor 0.75mm (AWG22)

Material stranded bare copper (7xAWG30)

2. Insulation

Material PE

Diameter over insulation $1.25 \pm 0.05 \text{ mm}$ Wallthickness 0.25 mm

3. Overall Cabling

Colour code black-red-white-green-brown-blue

4. Outer shield

Shield Beldfoil®)

Shield Material Aluminium / Polyester tape

Shield Thickness Alu $9 \mu m$ Shield coverage 100%

Drainwire AWG24 (7xAWG32) tinned Cu

4. Sheath

REQUIREMENTS AND TEST METHODS

Electrical:

Testvoltage conductor-conductor 2500 VDC, 3 seconds Testvoltage conductor-screen 2500 VDC, 3 seconds

Voltage rating 300 V RMS

Maximum continues current per conductor @ 25 °C 2.0 A per conductor @ 25 °C



TECHNICAL DATA SHEET

concept

code

version 1

date **2004-04-27** page **2/2**

4504FE NON-PAIRED

Mechanical and physical:

Temperature range processing and operating

-20 to +70 °C

Temperature range storage

-30 to +70 °C

Minimum bending/setting radius

5*D/10*D

Maximum pulling tension

28 N

Halogen free according to IEC 60754-1

Non dense smoke according to IEC 61034-1 and 61034-2

Non corrosive gas according to IEC 60754-2 Flame Retardant according to IEC 60332-1

MARKING

NEW GENERATION(R) BY BELDEN 4504FE HALOGEN FREE 70C 6C22 SHIELDED + sequential meter marking.