

## SECTION 1: Identification of the substance/mixture and of the company/ undertaking

- 1.1 Product identifier
- Trade name: **46-79-B fl. red**
- Registration number  
The ingredients of this ink have been pre-registered according to 1907/2006/EC (REACH)
- 1.2 Relevant identified uses of the substance or mixture and uses advised against  
Currently no such applications are identified
- Application of the substance / the mixture  
Highlighter Ink  
water based highlighter ink
- 1.3 Details of the supplier of the safety data sheet
- Manufacturer/Supplier:  
SHANGHAI DOKUMENTAL INK Co. Ltd.  
No. 18-3, Mao Jia Road  
Luodian Town, Baoshan District  
Shanghai 201908 , P.R. China  
Tel.: 86-21-66864551 / 66864542
- Further information obtainable from:  
Ms. Cindy Song  
Email: cindy.song@dokumental.cn
- 1.4 Emergency telephone number:  
Mr. Bruce Gindelberger  
Tel.: mobile +86-13917914495  
Email:bruce.gindelberger@dokumental.cn

## SECTION 2: Hazards identification

- 2.1 Classification of the substance or mixture
- Classification according to Regulation (EC) No 1272/2008  
The product is not classified according to the CLP regulation.
- 2.2 Label elements
- Labelling according to Regulation (EC) No 1272/2008 Void
- Hazard pictograms Void
- Signal word Void
- Hazard statements Void
- 2.3 Other hazards
- Results of PBT and vPvB assessment
- PBT: Not applicable.
- vPvB: Not applicable.

## SECTION 3: Composition/information on ingredients

- 3.2 Chemical characterisation: Mixtures  
Mixture of the following substances, containing non-hazardous substances and colouring agents.
- Description: Mixture of substances listed below with nonhazardous additions.

### Dangerous components:

CAS: 65122-08-9	C.I.Basic Red 12 acetat	≤1,0%
EINECS: 265-479-2	☠ Acute Tox. 3, H301; ☠ Eye Dam. 1, H318; ☠ Aquatic Chronic 2, H411	

- Additional information: For the wording of the listed risk phrases refer to section 16.

## SECTION 4: First aid measures

- 4.1 Description of first aid measures
- General information: No special measures required.
- After inhalation: Supply fresh air; consult doctor in case of complaints.
- After skin contact: Generally the product does not irritate the skin.
- After eye contact: Rinse opened eye for several minutes under running water.
- After swallowing: If symptoms persist consult doctor.
- 4.2 Most important symptoms and effects, both acute and delayed  
No further relevant information available.
- 4.3 Indication of any immediate medical attention and special treatment needed  
No further relevant information available.

## SECTION 5: Firefighting measures

- 5.1 Extinguishing media
- Suitable extinguishing agents: Use fire extinguishing methods suitable to surrounding conditions.
- 5.2 Special hazards arising from the substance or mixture No further relevant information available.

(Contd. on page 2)

Trade name: 46-79-B fl. red

(Contd. of page 1)

- 5.3 Advice for firefighters
- Protective equipment: No special measures required.

## SECTION 6: Accidental release measures

- 6.1 Personal precautions, protective equipment and emergency procedures Wear protective clothing.
- 6.2 Environmental precautions:  
Dilute with plenty of water.  
Do not allow to enter sewers/ surface or ground water.
- 6.3 Methods and material for containment and cleaning up:  
Absorb with liquid-binding material (sand, diatomite, acid binders, universal binders, sawdust).
- 6.4 Reference to other sections  
No dangerous substances are released.  
See Section 7 for information on safe handling.  
See Section 8 for information on personal protection equipment.  
See Section 13 for disposal information.

## SECTION 7: Handling and storage

- 7.1 Precautions for safe handling  
No special measures required.  
Ensure good ventilation/exhaustion at the workplace.
- Information about fire - and explosion protection: No special measures required.
- 7.2 Conditions for safe storage, including any incompatibilities
- Storage:  
Requirements to be met by storerooms and receptacles: No special requirements.
- Information about storage in one common storage facility: Not required.
- Further information about storage conditions: None.
- 7.3 Specific end use(s) No further relevant information available.

## SECTION 8: Exposure controls/personal protection

- Additional information about design of technical facilities: No further data; see item 7.
- 8.1 Control parameters
- Ingredients with limit values that require monitoring at the workplace:  
The product does not contain any relevant quantities of materials with critical values that have to be monitored at the workplace.
- Additional information: The lists valid during the making were used as basis.
- 8.2 Exposure controls
- Personal protective equipment:
- General protective and hygienic measures:  
The usual precautionary measures are to be adhered to when handling chemicals.
- Respiratory protection: Not required.
- Protection of hands:  
The glove material has to be impermeable and resistant to the product/ the substance/ the preparation.  
Due to missing tests no recommendation to the glove material can be given for the product/ the preparation/ the chemical mixture.  
Selection of the glove material on consideration of the penetration times, rates of diffusion and the degradation
- Material of gloves  
The selection of the suitable gloves does not only depend on the material, but also on further marks of quality and varies from manufacturer to manufacturer. As the product is a preparation of several substances, the resistance of the glove material can not be calculated in advance and has therefore to be checked prior to the application.
- Penetration time of glove material  
The exact break through time has to be found out by the manufacturer of the protective gloves and has to be observed.
- Eye protection: Goggles recommended during refilling

## SECTION 9: Physical and chemical properties

- 9.1 Information on basic physical and chemical properties
- General Information
- Appearance:  
Form: Fluid  
Colour: According to product specification
- Odour: Product specific

(Contd. on page 3)

Trade name: 46-79-B fl. red

(Contd. of page 2)

· Odour threshold:	Not determined.
· Important information on protection of health and environment, and on safety.	-
· pH-value at 20 °C:	7,6
· Change in condition	
Melting point/Melting range:	Undetermined.
Boiling point/Boiling range:	100 °C
· Flash point:	160 °C
· Flammability (solid, gaseous):	Not applicable.
· Ignition temperature:	400 °C
· Decomposition temperature:	Not determined.
· Self-igniting:	Product is not selfigniting.
· Danger of explosion:	Not determined.
· Explosion limits:	
Lower:	Not determined.
Upper:	Not determined.
· Vapour pressure at 20 °C:	23 hPa
· Density at 20 °C:	1,05 g/cm <sup>3</sup>
· Relative density	Not determined.
· Vapour density	Not determined.
· Evaporation rate	Not determined.
· Solubility in / Miscibility with water:	Fully miscible.
· Partition coefficient (n-octanol/water):	Not determined.
· Viscosity:	
Dynamic:	Not determined.
Kinematic:	Not determined.
· Solvent content:	
Organic solvents:	0,0 %
Water:	69,3 %
· Solids content:	0,1 %
· 9.2 Other information	The physical and chemical properties given in Section 9.1 are rough data only, which are partially derived from the component's data of the mixture. These data are no binding product specifications.

## SECTION 10: Stability and reactivity

- 10.1 Reactivity
- 10.2 Chemical stability
- Thermal decomposition / conditions to be avoided:  
No decomposition if used according to specifications.
- 10.3 Possibility of hazardous reactions No dangerous reactions known.
- 10.4 Conditions to avoid No further relevant information available.
- 10.5 Incompatible materials: No further relevant information available.
- 10.6 Hazardous decomposition products: No dangerous decomposition products known.

## SECTION 11: Toxicological information

- 11.1 Information on toxicological effects
- Acute toxicity
- Primary irritant effect:
- Skin corrosion/irritation No irritant effect.
- Serious eye damage/irritation No irritating effect.
- Respiratory or skin sensitisation No sensitising effects known.
- Additional toxicological information:  
The product is not subject to classification according to the calculation method of the General EU Classification Guidelines for Preparations as issued in the latest version.  
When used and handled according to specifications, the product does not have any harmful effects to our experience and the information provided to us.

EU  
(Contd. on page 4)

Trade name: 46-79-B fl. red

(Contd. of page 3)

## SECTION 12: Ecological information

- **12.1 Toxicity**
- **Aquatic toxicity:** No further relevant information available.
- **12.2 Persistence and degradability** No further relevant information available.
- **12.3 Bioaccumulative potential** No further relevant information available.
- **12.4 Mobility in soil** No further relevant information available.
- **Additional ecological information:**
- **General notes:**  
Water hazard class 1 (German Regulation) (Self-assessment): slightly hazardous for water  
Do not allow undiluted product or large quantities of it to reach ground water, water course or sewage system.
- **12.5 Results of PBT and vPvB assessment**
- **PBT:** Not applicable.
- **vPvB:** Not applicable.
- **12.6 Other adverse effects** No further relevant information available.

## SECTION 13: Disposal considerations

- **13.1 Waste treatment methods**
- **Recommendation** Smaller quantities can be disposed of with household waste.
- **Uncleaned packaging:**
- **Recommendation:** Disposal must be made according to official regulations.
- **Recommended cleansing agents:** Water, if necessary together with cleansing agents.

## SECTION 14: Transport information

- |   |                 |
|---|-----------------|
| · <b>14.1 UN-Number</b>   |                 |
| · <b>ADR, ADN, IMDG, IATA</b>   | Void            |
| · <b>14.2 UN proper shipping name</b>   |                 |
| · <b>ADR, ADN, IMDG, IATA</b>   | Void            |
| · <b>14.3 Transport hazard class(es)</b>  |                 |
| · <b>ADR, ADN, IMDG, IATA</b>   |                 |
| · <b>Class</b>  | Void            |
| · <b>14.4 Packing group</b>   |                 |
| · <b>ADR, IMDG, IATA</b>  | Void            |
| · <b>14.5 Environmental hazards:</b>  |                 |
| · <b>Marine pollutant:</b>  | No              |
| · <b>14.6 Special precautions for user</b>  | Not applicable. |
| · <b>14.7 Transport in bulk according to Annex II of MARPOL73/78 and the IBC Code</b> | Not applicable. |
| · <b>UN "Model Regulation":</b>   | -               |

## SECTION 15: Regulatory information

- **15.1 Safety, health and environmental regulations/legislation specific for the substance or mixture**
- **Directive 2012/18/EU**
- **Named dangerous substances - ANNEX I** None of the ingredients is listed.
- **National regulations:**
- **Technical instructions (air):**

Class	Share in %
I	≤1.0

- **Waterhazard class:** Water hazard class 1 (Self-assessment): slightly hazardous for water.
- **15.2 Chemical safety assessment:** A Chemical Safety Assessment has not been carried out.

## SECTION 16: Other information

This information is based on our present knowledge. However, this shall not constitute a guarantee for any specific product features and shall not establish a legally valid contractual relationship.

- **Relevant phrases**
- H301 Toxic if swallowed.
- H318 Causes serious eye damage.
- H411 Toxic to aquatic life with long lasting effects.

(Contd. on page 5)

Trade name: 46-79-B fl. red

(Contd. of page 4)

· **Abbreviations and acronyms:**

*RID: Règlement international concernant le transport des marchandises dangereuses par chemin de fer (Regulations Concerning the International Transport of Dangerous Goods by Rail)*  
*ICAO: International Civil Aviation Organisation*  
*ADR: Accord européen sur le transport des marchandises dangereuses par Route (European Agreement concerning the International Carriage of Dangerous Goods by Road)*  
*IMDG: International Maritime Code for Dangerous Goods*  
*IATA: International Air Transport Association*  
*GHS: Globally Harmonised System of Classification and Labelling of Chemicals*  
*ELINECS: European Inventory of Existing Commercial Chemical Substances*  
*ELINCS: European List of Notified Chemical Substances*  
*CAS: Chemical Abstracts Service (division of the American Chemical Society)*  
*Acute Tox. 3: Acute toxicity, Hazard Category 3*  
*Eye Dam. 1: Serious eye damage/eye irritation, Hazard Category 1*  
*Aquatic Chronic 2: Hazardous to the aquatic environment - Chronic Hazard, Category 2*

· **\* Data compared to the previous version altered.**

EU