

## JALAS® 1718 ZENIT EASYROLL

EN ISO 20345:2011, S3 SRC

### PROPERTIES

Highest level of protection, excellent grip, perfect fit, extra comfortable, excellent shock absorption

### SPECIFICATION

TYPE OF SHOE Safety footwear, boots/Ankle boots

NAIL PROTECTION MATERIAL Steel

FITTING Regular 36-47

COLLECTION Zenit

PLATFORM Zenit

UPPER MATERIAL PU-coated leather, split leather

PRONOSE MATERIAL PU

TOECAP MATERIAL Aluminium

LINING MATERIAL Polyester, polyamide

SOLE MATERIAL PU midsole, RPU outsole

INSOLE FX2 Supreme

INSOLE MATERIAL Textile, soft EVA, polyester-based conductive thread, merino wool, double shock absorption zones in Poron® XRD®

FASTENING Boa®

COLOUR Black, grey, red



**ZENIT**  
COLLECTION



The product features remain unchanged only when insoles recommended by the manufacturer are used. All values for the specified product are indicated without tolerances and may vary to actual value for individual products. We reserve the right to modify or update the information in this document without prior notice.

2018-01-03



SP Technical research institute of Sweden

www.ejendals.com

## JALAS® 1718 ZENIT EASYROLL

### FEATURES

ProNose toe reinforcement, oil-resistant outsole, anti-static properties, bellows tongue, padded boot shaft, ventilating insole, quick-tie, stabilizer, pull loops, water repellent, double shock absorption zones, conforms with IEC 61340-5-1 (ESD)

### PRIMARY PROTECTION

Prevents risk of: toe injuries, nail penetration, antistatic

### PRIMARY ENVIRONMENTS OF USE

Outdoors, all-year use, environments with risk for outsole penetration



Aluminium toecap



Anti-static properties



Nail protection in steel



ESD



Water repellent



Oil-resistant outsole



ProNose toe reinforcement



Ergothon Shock Absorption System



Stabilizer

The product features remain unchanged only when insoles recommended by the manufacturer are used. All values for the specified product are indicated without tolerances and may vary to actual value for individual products. We reserve the right to modify or update the information in this document without prior notice.

2018-01-03

2(3)

**ejendals**  
PROTECTING HANDS AND FEET

**EJENDALS AB**

Box 7, SE-793 21 Leksand, Sweden

Phone +46 (0) 247 360 00

Fax +46 (0) 247 360 10

info@ejendals.com

order@ejendals.com

www.ejendals.com

# JALAS® 1718 ZENIT EASYROLL

**COMPLIANCE**  
EN ISO 20345:2011

**COMPLIANCE DESCRIPTION**

SB: Footwear with toe protection tested with 200 J impact and 15kN compression force (includes oil resistant outsole)

S1: Footwear made from leather and other materials excluding all-rubber or all-polymeric footwear + closed seat region + SB + A + E

S2: S1 + WRU

S3: S2 + P

WRU: Water-resistant upper

P: Penetration-resistant outsole

A: Electrical resistance (between 0.1-1000 Mega Ohms)

E: Energy absorption in the heel area (tested at 20 Joules)

SRA: Slip-resistance on ceramic tile floor with Sodium lauryl sulphate solution

SRB: Slip-resistance on steel floor with glycerol

SRC: SRA + SRB

IEC 61340-5-1: Electrostatic Discharge (ESD) resistance below 35 megaohm

BGR 191: Orthopedic footwear adjustment according to German BGR 191. Footwear is tested with adjusted orthopedic insoles in accordance with EN ISO 20345 standard



Aluminium toecap



Anti-static properties



Nail protection in steel



ESD



Water repellent



Oil-resistant outsole



ProNose toe reinforcement



ErgoShock Absorption System



Stabilizer

The product features remain unchanged only when insoles recommended by the manufacturer are used. All values for the specified product are indicated without tolerances and may vary to actual value for individual products. We reserve the right to modify or update the information in this document without prior notice.

2018-01-03

3(3)

**ejendals**  
PROTECTING HANDS AND FEET

**EJENDALS AB**

Box 7, SE-793 21 Leksand, Sweden

Phone +46 (0) 247 360 00

Fax +46 (0) 247 360 10

info@ejendals.com

order@ejendals.com

www.ejendals.com