

# GN 165.1 | Connecting clamps with base

for linear actuators, aluminium





- 1
- 2
- 3
- 4
- 5
- 6
- 7
- 8
- 9
- 10
- 11
- 12
- 13
- 14
- 15
- 16
- 17
- 18

## MATERIAL

Aluminium, epoxy resin coating, RAL 9005 black colour, matte finish.  
AISI 304 stainless steel screws and nuts.  
Connector nut in natural steel.

## FEATURES AND APPLICATIONS

GN 165.1 bases for connecting clamps can normally be matched with square linear actuators GN 291.1 (see page 1376).  
By clamping the guide hole  $s$  it is possible to adjust the actuator positioning and to lock the slider after having set up the final position.  
The clamping screw  $d_2$  may be replaced by clamping kits GN 911 (see page 1372).



Code	Description	s										d2 Clamping kit	$\Delta$		
		d1 Square hole	d2	d3	k	l1	l2	t	x1	x2	y1			y2	
GN.49406	GN 165.1-V30-2-SW	6.5	30	M8	M4	58	69	46	7	75	60	75	60	GN 911-M8-32	270
GN.49416	GN 165.1-V40-2-SW	11	40	M10	M5	91	98	70	14	115	90	119	90	GN 911-M10-55	920
GN.49426	GN 165.1-V50-2-SW	11	50	M10	M6	91	98	70	14	115	90	119	90	GN 911-M10-55	840

Connecting clamps