


PM1614



Electronic pressure sensor

PM-016-REA01-E-ZVG/US



A³ ACS C E CRN UL^{us} LISTED EHEDG Tested FCM FDA IO-Link Reg31

Product characteristics

| | | | |
|--|---|-----------------|----------------|
| Output signal | analogue signal; (configurable) | | |
| Measuring range | -1...16 bar | -14.6...232 psi | -0.1...1.6 MPa |
| Process connection | threaded connection G 1 external thread sealing cone | | |
| Application | | | |
| Special feature | Gold-plated contacts | | |
| Measuring element | ceramic-capacitive pressure measuring cell | | |
| Application | food and beverage industry | | |
| Media | viscous media and liquids with suspended particles; liquids and gases | | |
| Medium temperature [°C] | -25...125; (150 max. 1h) | | |
| Pressure rating | 75 bar | 1085 psi | 7.5 MPa |
| Min. bursting pressure | 250 bar | 3625 psi | 25 MPa |
| Vacuum resistance [mbar] | -1000 | | |
| Type of pressure | relative pressure; vacuum | | |
| No dead space | yes | | |
| MAWP (for applications according to CRN) [bar] | 55 | | |

PM1614

Electronic pressure sensor

PM-016-REA01-E-ZVG/US



| Electrical data | | | |
|------------------------------------|------------------------|--|-----------------|
| Operating voltage | [V] | 18...30 DC | |
| Min. insulation resistance | [MΩ] | 100; (500 V DC) | |
| Protection class | | III | |
| Reverse polarity protection | | yes | |
| Integrated watchdog | | yes | |
| 2-wire | | | |
| Current consumption | [mA] | 3.5...21.5 | |
| Power-on delay time | [s] | 1 | |
| 3-wire | | | |
| Current consumption | [mA] | < 45 | |
| Power-on delay time | [s] | 0.5 | |
| Inputs / outputs | | | |
| Number of inputs and outputs | | Number of analogue outputs: 1 | |
| Outputs | | | |
| Total number of outputs | | 1 | |
| Output signal | | analogue signal; (configurable) | |
| Number of analogue outputs | | 1 | |
| Analogue current output | [mA] | 4...20; (scalable) | |
| Max. load | [Ω] | 700; ($U_b = 24 \text{ V}$; $(U_b - 9 \text{ V}) / 21.5 \text{ mA}$) | |
| Short-circuit proof | | yes | |
| Overload protection | | yes | |
| Measuring/setting range | | | |
| Measuring range | | -1...16 bar | -0.1...1.6 MPa |
| Analogue start point | | -1...12.8 bar | -0.1...1.28 MPa |
| Analogue end point | | 2.2...16 bar | 0.22...1.6 MPa |
| In steps of | | 0.01 bar | 0.001 MPa |
| Factory setting | | ASP = 0.0 bar | AEP = 16.0 bar |
| Accuracy / deviations | | | |
| Repeatability | [% of the span] | < ± 0,1; (with temperature fluctuations < 10 K; Turn down 1:1) | |
| Characteristics deviation | [% of the span] | < ± 0,2 (DIN EN 61298-2); (incl. zero point and span error, non-linearity, hysteresis ; Turn down 1:1) | |
| Linearity deviation | [% of the span] | < ± 0,15; (Turn down 1:1) | |
| Hysteresis deviation | [% of the span] | < ± 0,15; (Turn down 1:1) | |
| Long-term stability | [% of the span] | < ± 0,1; (Turn down 1:1; per year) | |
| Temperature coefficient zero point | [% of the span / 10 K] | < ± 0,05; (0...70 °C) | |
| Temperature coefficient span | [% of the span / 10 K] | < ± 0,15; (0...70 °C) | |

PM1614




Electronic pressure sensor

PM-016-REA01-E-ZVG/US



| Response times | | |
|---|---------|---|
| Damping for the analogue output dAA | [s] | 0...4 |
| 2-wire | | |
| Step response time analogue output | [ms] | 30 |
| 3-wire | | |
| Step response time analogue output | [ms] | 7 |
| Interfaces | | |
| Communication interface | | IO-Link |
| Transmission type | | COM2 (38,4 kBaud) |
| IO-Link revision | | 1.1 |
| IO-Link device ID | | 661 d / 00 02 95 h |
| Profiles | | Digital Measuring Sensor (0x000A), Identification and Diagnosis (0x4000) |
| SIO mode | | no |
| Required master port type | | A |
| Process data analogue | | 3 |
| Min. process cycle time | [ms] | 3.2 |
| Operating conditions | | |
| Ambient temperature | [°C] | -25...80 |
| Storage temperature | [°C] | -40...100 |
| Protection | | IP 67; IP 68; IP 69K |
| Tests / approvals | | |
| EMC | | DIN EN 61000-6-2 DIN EN 61000-6-3 |
| Shock resistance | | DIN EN 60068-2-27 |
| Vibration resistance | | DIN EN 60068-2-6 |
| MTTF | [years] | 323 |
| Note on approval | | factory certificate available as download at www.factory-certificate.ifm |
| UL approval | | UL Approval no. |
| | | J022 |
| Mechanical data | | |
| Weight | [g] | 304.7 |
| Materials | | stainless steel (1.4404 / 316L); PBT |
| Materials (wetted parts) | | ceramics (99.9 % Al2O3); PTFE; stainless steel (1.4435 / 316L); surface characteristics: Ra < 0,4 / Rz 4 |
| Min. pressure cycles | | 100 million |
| Tightening torque | [Nm] | 20 |
| Process connection | | threaded connection G 1 external thread sealing cone |
| Displays / operating elements | | |
| Display unit | | bar; psi; MPa |
| Remarks | | |
| Pack quantity | | 1 pcs. |
| Electrical connection | | |
| Connector: 1 x M12; Contacts: gold-plated | | |

Electronic pressure sensor

PM-016-REA01-E-ZVG/US



Connection



1 connection for 2-wire operation (analogue)

2 connection for 3-wire operation (analogue / IO-Link)

OUT1 : IO-Link

OUT2 : analogue output