

EC Material Safety Data Sheet

in accordance with Commission Directive 91/155/EEC and 2001/58/EC

Saeco Cleaning Powder

Product number: 3532

MSDS revised on: 06.11.2006

print date: 23.01.2007

page: 1 of 5

1. Identification of the Preparation and of the company/undertaking

Trade name: Saeco Cleaning Powder

Use of the preparation: (2) detergent; for professional , manual use

Manufacturer/distributor or importer:

Chemische Fabrik Dr. Weigert GmbH & Co. KG, Mühlenhagen 85, D-20539 Hamburg
Telefon: +49 (0)40/78960-0 Telefax: +49 (0)40/78960-120 E-Mail: info@drweigert.de

Emergency Call (national poison control centre) :

2. Composition/information on ingredients

Hazardous ingredients and their classification as pure substances acc. to Dangerous Preparation Directive 99/45/EC
For product classification see heading 3 and 15 ! For full text of R phrases see heading 16!

Hazardous ingredient		%	Symbols	R-Sentences
CAS: 584-08-7 EINECS: 209-529-3	potassium carbonate	> 30	Xi	36,37,38

3. Hazards Identification

R 36/38 Irritating to eyes and skin.

4. First aid measures

General information: Change clothing which has become wetted with the substance.

After contact with the skin: Wash off affected skin areas immediately and rinse with plenty of water.

After contact with the eyes: Rinse the opened eye with plenty of water.

If the substance is swallowed: Rinse out mouth and immediately ,drink 1 glass of water.

Do not provoke vomiting. Consult a doctor in case of continuing unwellness.

EC Material Safety Data Sheet

in accordance with Commission Directive 91/155/EEC and 2001/58/EC

Saeco Cleaning Powder

Product number: 3532

MSDS revised on: 06.11.2006

print date: 23.01.2007

page: 2 of 5

5. Fire-fighting measures

Suitable extinguishing agents:

water (spray), foam, extinguishing powder, carbon dioxide. Adapt firefighting operation to surrounding fire.

Extinguishing agents which are unsuitable for reasons of safety:

none specified

Special exposure hazards arising by the preparation itself, combustion products, resulting gases:

Oxygen. Oxygen supports the fire. Danger of appearance of overpressure and bursting in case of decomposition in sealed containers and tubes.

Special protective equipment for fire fighters additional to sec. 8:

In the event of fire wear self-contained breathing apparatus.

Further remarks:

Use water spray to cool unopened containers.

6. Accidental release measures

Personal precautions additional to section 8:

none

Environmental precautions:

Do not flush concentrate into drains, surface or ground waters.

Methods for cleaning up:

Tidy up mechanically (e.g. broom) and dispose of according to local provisions.

Flush away minor amounts with plenty of water.

7. Handling and storage

Handling: No special measures required if used correctly.

Storage: Keep containers tightly closed. Protect against humidity and water.

8. Exposure controls / personal protection

Additional information on the design of technical plant: No special measures required.

Components with occupational threshold limit values:

CAS-Nr.	Substance	mg/m ³ ; ml/m ³
---------	-----------	---------------------------------------

Personal safety equipment:

Handschutz: Protective gloves made out of nitril or butyl rubber of category III according to EN 374. Please follow the instruction of the manufacturers of gloves for expected breakthrough times in relation to the special conditions of the working place like amount of mechanical stress or duration of dermal exposure.

For short term contact with ready-to-use dilutions without mechanical stress gloves out of rubber or latex are sufficient.

EC Material Safety Data Sheet

in accordance with Commission Directive 91/155/EEC and 2001/58/EC

Saeco Cleaning Powder

Product number: 3532

MSDS revised on: 06.11.2006

print date: 23.01.2007

page: 3 of 5

9. Physical and chemical properties relevant for the preparation

Form: Pulver	Flash n.a.
Colour: white	pH-value (20°C) approx.: 11,4 (10%)
Odour: characteristic	Result of Acid-/Alkali reserve : -
Density (20 ° C) g/cm ³ approx. -	Solubility in water ((20 ° C): soluble
Bulk density g/l approx.: 1030	
Viscosity (20 ° C) mPa s : -	

n.a. : nicht anwendbar/ not applicable/ pas applicable; “-” : keine Daten, no data, aucunes données

10. Stability and reactivity

Conditions to be avoided: Does not decompose if used as directed..

Substances to be avoided: Do not mix with other products.

Dangerous decomposition products: None if used as per instructions.

11. Toxicological information

The assessment of the toxicological properties of the product is based exclusively upon the data of the raw materials and the classification criteria (calculation method) of the European Dangerous Preparation Directive 99/45/EC.

No test data are available for the preparation.

After contact with the concentrate hazards as mentioned under section 3 and 15 resp. may occur.

12. Ecological informations

The assessment of the ecotoxicological properties of the product is based exclusively upon the data of the raw materials and the classification criteria (calculation method) of the European Dangerous Preparation Directive 99/45/EC.

No test data are available for the preparation.

Do not allow the concentrate to contaminate the public sewage system, surface water or ground water. The local regulations (e.g. pH value) must be observed when discharging dilute application solutions into the public sewage system. The function of public sewage-treatment plants is not impaired if adequately diluted solutions within the permitted pH range are discharged.

German water hazard class (WGK): 1 - low hazard to waters

13. Information on disposal

Preparation: Please review national or regional provisions prior to disposal! Recommendation: Incineration by an authorized plant. EWC code number recommendation (European Waste catalogue) :070608 “Waste from manufacturing, trading and use of ...detergents, soaps, disinfectants and cosmetics...”; for aerosols only: EWC 160504 “Gases in aerosol cans containing dangerous substances”.

Packagings (not cleaned): Contaminated packagings out of HDPE should be restlessly emptied. They are then suitable for recycling, incineration or landfilling. Please review national or regional provisions prior to disposal!

EC Material Safety Data Sheet

in accordance with Commission Directive 91/155/EEC and 2001/58/EC

Saeco Cleaning Powder

Product number: 3532

MSDS revised on: 06.11.2006

print date: 23.01.2007

page: 4 of 5

14. Transport informations According to harmonized regulations ADR/RID/IMDG-Code/IATA-DGR/ICAO-TI:

UN Number: -

Proper Shipping Name:

-

Class - **Packaging Group:** - **Marine Pollutant:** **EmS** -

Hazard Label(s) No - ,

remarks:

15. Regulations !!!

Classification and labelling of the product as delivered according to the European Dangerous Preparation Directive 1999/45/EC:

Symbol(s): Xi Irritant

contains:

Risk phrases:

R 36/38 Irritating to eyes and skin.

Safety phrases:

S 2 Keep out of reach of children.

S 26 In case of contact with eyes, rinse immediately with plenty of water and seek medical advice.

S 37 Wear suitable gloves.

S 46 If swallowed, seek medical advice immediately and show this container or label.

Additional Remarks:

EC Material Safety Data Sheet

in accordance with Commission Directive 91/155/EEC and 2001/58/EC

Saeco Cleaning Powder

Product number: 3532

MSDS revised on: 06.11.2006

print date: 23.01.2007

page: 5 of 5

16. Additional information

Full text of the R phrases mentioned in chapter 2

R 36 Irritating to eyes.
R 37 Irritating to respiratory system.
R 38 Irritating to skin.

Recommended restrictions on use :

- **Ingredients according to European Regulation(EC) No 648/2004 on detergents**
 - **Active substances for biocides/disinfectants (if applicable)**
- > 30 % : phosphates,

Further information :

The above information which is given to the best of our knowledge and on the basis of experience to date is intended to describe our product with regard to possible safety requirements but does not constitute a description of quality or assurance of specific characteristics. Any modification is marked by !!! in the heading of relevant chapter.