

SVJB clamp holder, positive, right

For copy, longitudinal and face turning with VB indexable insert

ATORN[®]

Application


For copy, longitudinal and face turning with VB indexable insert, 35°

Version

- precision-manufactured steel carrier, bronzed, hardened, type S, attack angle 107.5°, tip angle 35°, clearance angle 5°
- SVJBR 1212 F11

Advantage

- Very streamlined geometry, optimised for contour lathe work
- Positive geometry for the body ensures low cutting forces
- Very good surface quality for medium infeed and finishing



Art. no.	17836 321
ISO name	SVJB R/L 1212 F11
Shaft height	12 mm
Shank width	12 mm
Length	80 mm
Length of head	21.5 mm
Programming size	16 mm
Suitable for indexable inserts	VB.. 1103..
Tool design	Left

EAN-Code

4050293563467