

Isolating transformer TIM 1000



Picture shows TIM 100


Advantages

- Safe galvanic isolation
- Integrated short-circuit and overload protection
- Double output voltage for series or parallel connection
- Very good moisture protection and low noise thanks to XtraDenseFill resin encapsulation (up to 300 VA)
- Screw terminals under cover with strain relief

Applications

Isolating transformer for the safe electrical isolation of the input and output sides. The transformer may be used to set up protective separation as a protective measure in accordance with VDE 0100.

Sample application



Standards

Isolating transformer
to: VDE 0570 Part 2-4, DIN EN 61558-2-4, EN 61558-2-4, IEC 61558-2-4

Approvals




VDE



Isolating transformer TIM 1000

Type		TIM 1000
Electrical data	Input	
	Rated frequency	50 - 60 Hz
	Rated input voltage	230 Vac
	Output	
	Rated output voltage	2 x 115 Vac
	Rated Power	1,000 VA
	No-load voltage (app. x factor)	1.02
	No-load loss (typ.)	27.00 W
	Efficiency	95.0 %
	Approvals	
	Approvals	VDE, cURus
	Environment	
	Ambient temperature max.	40 °C
	Safety and protection	
	Type	Encapsulated in metal housing
	Insulation class	B
	Protection index	IP 20
	Safety class	I
	Short circuit strength	non-inherently short-circuit proof
Test voltage	3,750 Vac, 50 Hz	
Order numbers		
Order Number	TIM 1000	

Type		TIM 1000
Mechanical data	Terminal and mounting	
	Fixing method	Fixing holes in the housing
	Terminals	Screw-type terminals
	Measures and weights	
	Weight	17.10 kg



Subject to change.