

## Self-locking threaded support bolt

Quick and easy-to-use attachment point

**HALDER**

### Application:

For lifting loads. The threaded support bolt is inserted into a threaded hole and secures itself. In contrast to a ring screw, this eliminates time-consuming screwing and unscrewing.

### Execution:

- Stop point with self-locking thread
- Shackles made of heat-treated steel, tempered, manganese phosphate-coated
- Stainless steel 1.4542 thread element, precipitation-hardened
- Movable shackle
- Loosen the safety bar to prevent accidental release
- High-strength, precipitation-hardened bolts
- Aluminium press stud
- TÜV tested - in accordance with DIN EN 13155

### Advantage:

- Time savings of up to 95% compared to conventional ring bolts



<b>Art. no.</b>	<b>77241 101</b>
<b>Brand</b>	HALDER
<b>Manufacturer Part Number</b>	22352.0012
<b>Thread dimension</b>	M12
<b>Load-carrying capacity</b>	632 kg
<b>Material of shackles</b>	Steel tempered
<b>Surface of the shackle</b>	Manganese phosphated
<b>Material of bolt</b>	Steel tempered
<b>Material of spring</b>	Corrosion resistant steel
<b>Material of push knob</b>	Aluminium
<b>Weight</b>	220 g
<b>Max. temperature</b>	250 °C
<b>Design</b>	Self-locking
<b>Operation</b>	By pressing the button
<b>With corrosion protection</b>	Yes
<b>Length to centre of bolt</b>	17 mm
<b>Bolt length</b>	24 mm
<b>Length 3</b>	25.7 mm
<b>Bolt length above</b>	36 mm
<b>Interior height</b>	27 mm
<b>Internal width</b>	30 mm
<b>External width</b>	49 mm
<b>Height</b>	87.5 mm
<b>Outer diameter</b>	10.07 mm
<b>Diameter bolt top</b>	21.5 mm
<b>Thread length</b>	12 mm
<b>Gross Weight</b>	0.235 kg
<b>Product Group</b>	7EC

### EAN

4030618701866