RMS and peak acceleration loop powered sensors

PCC420A series



Wilcoxon's PCC420A series sensors provide a 4-20 mA output proportional to vibration, allowing for continuous trending of overall machine vibration. This trend data alerts users to changing machine conditions and helps guide maintenance in prioritizing the need for service. The choice of RMS or peak output allows you to choose the sensor that best fits your requirements.



Table 1: PCC420Ax-yy-C model selection guide

x (4-20 mA output type)	yy (4-20 mA full scale)	C (output connector)
R = RMS output, acceleration P = calculated peak output, acceleration	05 = 5 g (49 m/sec ²) 10 = 10 g (98 m/sec ²) 20 = 20 g (196 m/sec ²) 50 = 50 g (490 m/sec ²)	R6 = 2 pin, MIL-C-5015 M12 = 4 pin, M12

Certifications



Key features

- True RMS or calculated peak output
- Connector options: 2-pin MIL-C-5015 or 4-pin M12
- Easily integrated into existing process control systems
- Compact housing for applications with height restrictions
- Manufactured in an approved ISO 9001 facility

Note: Due to continuous process improvement, specifications are subject to change without notice. This document is cleared for public release.

Tel: +1 (301) 330-8811 Fax: +1 (301) 330-8873 info@wilcoxon.com

RMS and peak acceleration loop powered sensors

Wilcoxon SENSING TECHNOLOGIES

PCC420A series

SPECIFICATIONS


Full scale, 20 mA, ±5%		see Table 1 on page 1
Frequency response:	±10%	10 Hz - 1.0 kHz
	±3 dB	1.0 Hz - 2.0 kHz
Repeatability		±2%
Transverse sensitivity, max		5%
Power requirements, 2-wire loop power: Voltage at sensor terminals		12 - 30 VDC
Loop resistance ¹ at 24 VDC, max		700 Ω
Turn on time, 4-20 mA loop		<30 seconds
Grounding		case isolated, internally shielded
Operating temperature range		–40° to +105° C
Vibration limit		250 g peak
Shock limit		2,500 g peak
Sealing		hermetic
Sensing element design		PZT, shear
Weight		120 grams
Case material		316L stainless steel
Mounting		1/4-28 UNF tapped hole
Output connector		2-pin MIL-C-5015 or 4-pin M12
Mating connector		R6 type
Recommended cabling		J9T2A
		·······


Notes: ¹ Maximum loop resistance (R_L) can be calculated by: $R_L = \frac{V_{DC power} - 10 \text{ V}}{20 \text{ mA}}$

DC supply voltage	R _L (max resistance) ²	R _∟ (minimum wattage capability)³
12 VDC	100 Ω	1/8 watt
20 VDC	500 Ω	1/4 watt
24 VDC	700 Ω	1/2 watt
26 VDC	800 Ω	1/2 watt
30 VDC	1,000 Ω	1/2 watt


- 2 Lower resistance is allowed, greater than 10 Ω recommended.
- ³ Minimum R₁ wattage determined by: (0.0004 x R₁).

Accessories supplied: SF6 mounting stud; calibration data (level 2)





Connections (-R6 models)		
Function	Connector pin	
loop positive (+)	Α	
loop negative (-)	В	
ground	shell	



Connections (-M12 models)		
Function	Connector pin	
loop positive (+)	1	
loop negative (-)	2	
N/C	3	
N/C	4	
ground	shell	

Note: Due to continuous process improvement, specifications are subject to change without notice. This document is cleared for public release.

Tel: +1 (301) 330-8811 Fax: +1 (301) 330-8873 info@wilcoxon.com