

Modular drilling system TDMX drilling depth 12xD

For universal use up to 1300 N/mm², in diameter range of 16.00-32.00 mm

WIDIA 

Execution:

- Drilling depth 12xD
- Diameter range 16-32 mm

Advantage:

- Front clamping, possible to change the cutting body while clamped
- Up to 3x regrinding possible
- Polished chip grooves for better chip removal
- Types developed for material-specific applications



Art. no.	11232 230
Brand	WIDIA
Manufacturer Part Number	6681044
Suitable for min. cutting diameter	23 mm
Suitable for max. cutting diameter	23.99 mm
Shank diameter	25 mm
Length	385 mm
Cantilever length	329 mm
Effective length	288 mm
Shaft length	56 mm
Suitable for indexable inserts type	H
Max. drilling depth (D)	12xD
Coolant supply	Internal
Tool holding device	HA parallel shank
Bore type	Normal bore, Stud hole bore, Cross bore, Slanted exit, Slanted entry
Gross Weight	0.802 kg
Product Group	1XB