

Short taper-flange

Made of cast iron



Application:

For retroactive fastening of lathe chucks.

Execution:

- Ready-machined on machine side and chuck side, spindle heads with camlock fastening in accordance with DIN ISO 702-2 (formerly DIN 55029).

Art. no.	22510 120
Brand	BISON
Manufacturer Part Number	358245452700
Flange diameter	250 mm
Taper shank size	8
Pitch circle diameter	224 mm
Taper diameter	139.735 mm
Drill hole	136.1 mm
Ratio	200 mm
Number of bolts	6/4 pieces
Flange thickness	39 mm
Thread dimension	M12 x 6
Gross Weight	10.034 kg
Product Group	221

