



Neohm | Neohm R

TE Internal #: 1-1676915-4

Neohm R, Through-Hole Resistors, Precision Resistor, 6.3 x 2.3 mm, 2 Termination, Ammo Packed, .1 Passive Component Tolerance, Thin Film

[View on TE.com >](#)

Passive Components > Resistors > Through-Hole Resistors



Resistor Type: **Precision Resistor**

Passive Component Dimensions: **6.3 x 2.3 mm**

Number of Terminations: **2**

Packaging Method: **Ammo Packed**

Passive Component Tolerance: **.1 %**

Features

Product Type Features

| | |
|---------------|--------------------|
| Product Type | Fixed Resistor |
| Resistor Type | Precision Resistor |
| Element Type | Thin Film |

Configuration Features

| | |
|---------------------|---|
| Number of Resistors | 1 |
|---------------------|---|

Electrical Characteristics

| | |
|-----------------------------|-----------|
| Voltage Rating | 250 V |
| Passive Component Tolerance | .1 % |
| Resistance Class | 1kΩ – 1MΩ |
| Resistance Value | 76.8K Ω |
| Power Rating | .25 W |

Body Features

| | |
|-----------------------------|--------------|
| Passive Component Lead Type | Axial-Leaded |
|-----------------------------|--------------|

Termination Features

| | |
|---|---------------------|
| Number of Terminations | 2 |
| Passive Component Termination Material Type | Tinned Copper Leads |

Dimensions

| | |
|------------------------------|--------------|
| Passive Component Dimensions | 6.3 x 2.3 mm |
|------------------------------|--------------|



Usage Conditions

| | |
|-----------------------------|--------------|
| Operating Temperature Range | -65 – 155 °C |
| Temperature Coefficient | ±15 ppm/°C |

Packaging Features

| | |
|------------------|-------------|
| Packaging Method | Ammo Packed |
|------------------|-------------|

Product Compliance

For compliance documentation, visit the product page on [TE.com](https://www.te.com)>

| | |
|---|---|
| EU RoHS Directive 2011/65/EU | Compliant |
| EU ELV Directive 2000/53/EC | Compliant |
| China RoHS 2 Directive MIIT Order No 32, 2016 | No Restricted Materials Above Threshold |
| EU REACH Regulation (EC) No. 1907/2006 | Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JUN 2020 (209) SVHC > Threshold: Not Yet Reviewed |
| Halogen Content | Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free |
| Solder Process Capability | Reflow solder capable to 260°C |

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 2-1676913-6
YR1 0.1% 1K0



TE Part # 1622796-1
YR1 0.1% 100K



TE Part # 1622796-2
YR1 0.1% 100R



TE Part # 1622796-6
YR1 0.1% 10K



TE Part # 2-1676913-7
YR1 0.1% 1M0

Also in the Series | Neohm R



Eurocard Connectors(1)



Through-Hole Resistors(484)

Customers Also Bought




TE Part #1623714-2
FCB4 10K 5% HP



TE Part #1-1676914-1
YR1 0.1% 392K



TE Part #1625879-2
FRN50 5% 10R (S)



TE Part #9-1879664-3
H8 10K5 0.1% 15PPM



TE Part #1622424-1
LR1 1% 2R2



TE Part #1-1676914-2
YR1 0.1% 392R



TE Part #1622795-3
YR1 0.1% 3K01



TE Part #2-1419108-8
RTD14005F



Documents

CAD Files

[3D PDF](#)

3D

Customer View Model

[ENG_CVM_CVM_1-1676915-4_BA.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1-1676915-4_BA.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1-1676915-4_BA.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[1309350_PASSIVE_COMPONENT](#)

English

[Precision Metal Film Fixed Resistors - Type R Series - Tyco Electronics Passives](#)

English

Product Environmental Compliance

[Product Compliance](#)

English

[Product Compliance](#)

English