



ET 200PRO ERSE/RSSE HF ELECTRONIC REVERSING STARTER ELECTRONIC (SOFT) SWITCHING FULL MOTOR PROTECTION COMPRISING: ELECTRONIC OVERLOAD PROTECTION + THERMISTOR 3 AC 400V/5.5KW; 1.5A...(9A)12A BRAKE CONTACT AC 400V; 4DI HAN Q4/2 - HAN Q8/0

General technical data:		
product brand name		SIRIUS
Product designation		ET 200pro motor starters
Design of the product		reversing starter
Product function		
• Bus communication		Yes
• direct start		No
• reverse starting		Yes
• on-site operation		Yes
• Short circuit protection		Yes
Design of the switching contact		solid-state / thyristor / 2 phases
Product component Motor brake output		Yes
Trip class		CLASS 5, 10, 20 and 30 adjustable
Type of assignment		1
Product feature		
• brake control with 400 V AC		Yes
• brake control with 230 V AC		No
• brake control with 24 V DC		No
• brake control with 180 V DC		No
• brake control with 500 V DC		No
Type of voltage of the supply voltage for brake control required		AC
Supply voltage for brake control required	V	400
Surge voltage resistance Rated value	kV	6

maximum permissible voltage for safe isolation between main and auxiliary circuit	V	400
Equipment marking acc. to DIN EN 61346-2		Q
Equipment marking acc. to DIN 40719 extended according to IEC 204-2 acc. to IEC 750		A
Mounting type		screw fixing
Depth	mm	150
Height	mm	230
Width	mm	110

Main circuit:

Operating voltage Rated value	V	400 ... 500
Adjustable response value current of the current-dependent overload release	A	1.5 ... 12
Operating current at AC-3 at 400 V Rated value	A	12
Operating power at AC-3 at 400 V Rated value	W	5 500
Operating power for three-phase motors at 400 V at 50 Hz minimum	W	700
Operating power for three-phase motors at 400 V at 50 Hz maximum	W	5 500
Maximum short-circuit current breaking capacity (I _{cu}) at 400 V Rated value	A	100 000
Design of short-circuit protection		fuse
Number of poles for main current circuit		3
Type of the motor protection		full motor protection
Mechanical service life (switching cycles) of the main contacts typical		30 000 000

Control circuit/ Control:

Type of voltage of the control supply voltage		DC
Control supply voltage 1 for DC Final rated value	V	24
Control supply voltage 1 for DC Rated value		
• minimum permissible	V	20.4
• maximum permissible	V	28.8

Supply voltage:

Type of voltage of the supply voltage		DC
Supply voltage 1 for DC Final rated value	V	24
Supply voltage 1 for DC Rated value		
• minimum permissible	V	20.4
• maximum permissible	V	28.8

Ambient conditions:

Protection class IP		IP65
Ambient temperature		
• during operation	°C	-25 ... +55

<ul style="list-style-type: none"> during storage 	°C	-40 ... +70
<ul style="list-style-type: none"> during transport 	°C	-40 ... +70
Relative humidity during operation	%	5 ... 95
Vibration resistance		2g
Shock resistance		15g / 11 ms
Degree of pollution		3
Installation altitude at height above sea level maximum	m	3 500
mounting position		vertical, horizontal

Communication/ Protocol:

Protocol is supported		
<ul style="list-style-type: none"> PROFIBUS DP protocol 		Yes
<ul style="list-style-type: none"> PROFINET protocol 		Yes
<ul style="list-style-type: none"> AS-interface protocol 		No
Design of the interface PROFINET protocol		Yes
Type of electrical connection of the communication interface		via backplane bus

Connections/ Terminals:

Number of digital inputs		4
Number of sockets		
<ul style="list-style-type: none"> for digital input signals 		4
<ul style="list-style-type: none"> for digital output signals 		0
Product function		
<ul style="list-style-type: none"> digital inputs parameterizable 		Yes
<ul style="list-style-type: none"> digital outputs parameterizable 		No
Type of electrical connection		
<ul style="list-style-type: none"> 1 for digital input signals 		M12 socket
<ul style="list-style-type: none"> 2 for digital input signals 		M12 socket
<ul style="list-style-type: none"> 3 for digital input signals 		M12 socket
<ul style="list-style-type: none"> 4 for digital input signals 		M12 socket
Type of electrical connection		
<ul style="list-style-type: none"> at the manufacturer-specific device interface 		optical interface
<ul style="list-style-type: none"> for main energy infeed 		socket according to ISO23570
<ul style="list-style-type: none"> for load-side outgoing feeder 		socket according to ISO23570
<ul style="list-style-type: none"> for main energy transmission 		socket according to ISO23570
<ul style="list-style-type: none"> for supply voltage infeed 		via backplane bus
<ul style="list-style-type: none"> for supply voltage transmission 		via backplane bus
<ul style="list-style-type: none"> for main current circuit 		tab terminals

Certificate of suitability

Protection against electrical shock		finger-safe
--	--	-------------

Certificates/ approvals:



CCC



CSA



GOST



UL



EG-Konf.

**Test
Certificates**

other

[Type Test
Certificates/Test
Report](#)

[Environmental
Confirmations](#)

Further information

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/industrial-controls/catalogs>

Industry Mall (Online ordering system)

<http://www.siemens.com/industrymall>

Cax online generator



<http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mfb=3RK13045LS703AA3>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<http://support.automation.siemens.com/WW/view/en/3RK13045LS703AA3/all>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

<http://www.automation.siemens.com/bilddb/index.aspx?attID9=3RK13045LS703AA3&lang=en>



last modified:

09.03.2015